

## PRODUCT FACT SHEET

## STREAMLIGHT POLYSTINGER® RECHARGEABLE FLASHLIGHT

**MARKET** Law enforcement, Security, Fire & Rescue, Utility, Hardware/Tool, Automotive,

APPLICATIONS: Outdoor, Consumer.

**DESCRIPTION:** Compact yet powerful, the rechargeable PolyStinger is virtually indestructible due to

its super-tough nylon polymer construction.

CASE MATERIAL: Super-tough, non-conductive nylon polymer with non-slip grip, available in yellow,

black.

**DIMENSIONS:** Length: 7.34 in. (18.7 cm) Diameter: Major Diameter: 1.67 in. (4.24 cm)

Body Diameter: 1.15 in. (2.92 cm)

WEIGHT: 8.7 oz (247 grams)\*

LENS: Unbreakable polycarbonate lens with scratch-resistant coating.

LIGHT SOURCE: Xenon gas-filled bi-pin bulb, with a spare stored in the end cap, variable spot to flood

beam with 30-hour life

LIGHT OUTPUT: Up to 15,000 Peak beam candlepower. Bulb Rating: 125 Lumens typical

ON/OFF: Push-button head switch

**RUN TIME:** Up to one hour of continuous use

3-Cell, 3.6-Volt Nickel-cadmium sub-C battery is rechargeable up to 1000 times **BATTERY:** 

CHARGING: Ten hours to fully recharge on 100V, 120V, 230V or 240V AC, or 12V DC, 2.5-hour fast

charger or PiggyBack® charger model available.

**FEATURES:** LED charge-continuity indicator, Compact, snap-in charger holder that mounts in any

position, Serialized for positive identification

UL Listed for Class I, II, Division 2. APPROVALS\*\*

Most models meet applicable European Community Directives.

Limited lifetime warranty.

**OPTIONAL** 

WARRANTY:

**ACCESSORIES:** Safety wand, red lens, green lens, infra-red lens, ring holder, 5-unit bank charger,

holster, 2.5-Hour fast charger or PiggyBack® charger that allows for simultaneous

charging of light and a spare battery.

Assembled In The USA.

Document #102

Revised: 02/05/07 Rev: 1

Issued: 10/01/04

Page 1 of 1

<sup>\*</sup> With battery (included in purchase)

<sup>\*\*</sup> See product for specific ratings.