





Stylus Pro® Alkaline Battery-Powered LED Pen Light

FL1 STANDARD	C4 WHITE LED	GREEN LED
	48 LUMENS	5 LUMENS
	6h 15min	11h
	64m	17m
	1033 cd	73 cd



Case Material: Corrosion & water resistant, machined aircraft-grade aluminum alloy, Type II MIL-Spec anodize plating. Available in black, red, silver, and blue

Dimensions: Length: 5.3"; 134 mm Body Diameter: 0.6"; 15 mm

Weight: 1.64 oz.; 46.9 grams with battery (AAA Panasonic battery included with purchase)

Light Source: C4® LED technology, impervious to shock with a 30,000 hour lifetime.

On/Off: Push button tail switch

Battery: Two (2) "AAA" alkaline batteries

- Features:
- C4® LED technology for extreme brightness.
 - IPX4 rated for water resistant operation. All openings o-ring sealed.
 - 1 meter impact resistance tested.
 - Removable pocket clip

Approvals: Most models meet applicable European Community Directives.

Warranty: Streamlight warrants this product to be free of defects, including the LED, for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work as a result of a manufacturing defect for as long as you own it. This limited lifetime warranty excludes abuse, batteries, switches, electronics and normal wear and tear. Switches and electronics have a two (2) year warranty with proof of purchase.

Made in China

Item		UPC	Part#
Stylus Pro	Black with White LED	080926-66118-9	66118
Stylus Pro	Blue with White LED	080926-66122-6	66122
Stylus Pro	Silver with White LED	080926-66121-9	66121
Stylus Pro	Red with White LED	080926-66120-2	66120
Boot Switch Cover		N/A	660031

