## Stinger LED HL® RECHARGEABLE FLASHLIGHT

FL1 STANDARD	HIGH	MEDIUM	LOW
31/5	640 LUMENS	340 LUMENS	170 LUMENS
(1)	1h 15min	2h	4h
	297m	210m	148m
	22,000cd	11,000cd	5,500cd



Strobe runs for 3 hours

Designed for maximum illumination.

Material/ Lens 6000 series machined aircraft aluminum with non-slip rubberized comfort grip and anti-roll rubber ring.

Unbreakable polycarbonate lens with scratch-resistant coating

Dims/Weight Length: 8.41 in. (21.36 cm) Major Diameter: 1.62 in. (4.11 cm); Body Diameter: 1.17 in. (2.97 cm) 12.4 oz (352 grams)

Light Source C4® LED technology, shock-proof with a 50,000 hour lifetime. Deep-dish parabolic reflector produces a concentrated beam with optimum

peripheralillumination. Regulated run time provides consistent performance throughout battery life

Switch Multi-function, push-button switch designed for extremely long life; tested at 1 million actuations. Access high, medium, low and strobe

Battery 3-cell,3.6 Volt Ni-MH sub-C battery, rechargeable up to 1000 times

Charging Ten hours to fully recharge on AC or 12V DC, 2.5-hour fast charger or PiggyBack® charger model available

Features • Anti-roll ring included

· LED charge-continuity indicator, compact

• IPX4 Rated for water resistant operation

1 meter impact resistance tested
Snap-in charger holder that mounts in any position

Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, Warrantv replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.



Item Description	UPC	Part #
Stinger LED HL IEC Type C (230V) AC/12V DC – 2 holders	080926-75440-9	75440
Stinger LED HL 240V AC/12V DC -2 holders	080926-75448-5	75448
Stinger LED HL 120V AC/12V DC – 2 holders	080926-75430-0	75430
Stinger LED HL IEC Type A (100V) AC/12V DC – 2 holders	080926-75435-5	75435
Stinger LED HL IEC Type C (230V) AC	080926-75442-3	75442
Stinger LED HL 240V AC	080926-75449-2	75449
Stinger LED HL 120V AC	080926-75431-7	75431
Stinger LED HL Type A (100V) AC	080926-75436-2	75436
Stinger LED HL 12V DC	080926-75432-4	75432
Stinger LED HL 120V AC/12V DC – 1 PiggyBack	080926-75434-8	75434
Stinger LED HL 120V AC/12V DC – 1 PiggyBack - Kryptek	080926-75699-1	75699
Stinger LED HL 120V AC/12V DC - FC 2 holders	080926-75433-1	75433
Stinger LED HL without Charger	080926-75429-4	75429
Stinger LED HL without Charger - Kryptek	080926-75698-4	75698





Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
IEC Type A (100V/120V) AC charge cord	080926-22666-1	22666
Type C (230V) AC charge cord	080926-22061-4	22061
240V AC charge cord	080926-22241-0	22241
Charger Holder Stinger (10 Hour)	080926-75100-2	75100
Charger Holder Fast Charge (2.5 hour)	080926-75103-3	75103
5 Unit Bank Charger, 120V	080926-75400-3	75400
5 Unit Bank Fast Charger, 120V	080926-75401-6	75401
5 Unit Bank Charger, 230V	080926-75600-7	75600
5 Unit Bank Fast Charger, 230V	080926-75601-4	75601
PiggyBack® Charger Holder - Steady Charger & Battery	080926-75275-7	75275
Battery Stick (NiCd)	080926-75175-0	75175
Battery Stick (NiMH)	080926-75375-4	75375
Battery Stick (Lithium Ion)	080926-75176-7	75176

Item	UPC	Part #
Flip Lens IR	080926-75027-2	75027
Flip Lens Red	080926-75115-6	75115
Flip Lens Blue	080926-75116-3	75116
Flip Lens Green	080926-75117-0	75117
Safety Wand Blue	080926-75902-2	75902
Safety Wand Red	080926-75903-9	75903
Safety Wand Yellow	080926-75904-6	75904
Safety Wand White	080926-75908-4	75908
Safety Wand Glow in the Dark	080926-75913-8	75913
Ring Holder	080926-75906-0	75906
Duty Holster	080926-88053-5	88053
Holster	080926-75927-5	75927
Loop holster	080926-75928-8	75928
Leather holster: Plain - Stinger LED/PolyStinger LED	080926-75133-0	75133
Leather holster: Basket Weave - Stinger LED/		
PolyStinger LED Series	080926-75134-7	75134





