## ABM100-A-C







- Superior adhesive for long term reliability
  - 2-up mount configuration speeds liner removal and installation
  - 4-way cable tie entry makes part orientation fast and easy
  - Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
  - Used with PANDUIT cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

	Part Number	ABM100-A-C
	RoHS Compliancy Status	Compliant
	Part Description	4-Way Adhesive Backed Cable Tie Mount
+	Product Type	Cable Tie Mounts - Adhesive Backed
	Material	Nylon 6.6
*	Color	White
	UL Recognized	E136577
	Height (In.)	.20
•	Height (mm)	5.1
•	Length (In.)	1.00
	Length (mm)	25.4
	Width (In.)	1.00
	Width (mm)	25.4
	Adhesive Type	Rubber
	CE Compliant	CT-ACC1 / 10.96
	Environment	Indoors
	Max. Bundle Diameter (mm)	4.8
	Mounting Method	Adhesive Backed
	Pricing Description	Cable Tie Mount, Adh., 1"x1" (25.4mm x 25.4mm), WH
*	Screw Size	#6 (M3)
	Screw Size Metric	M3
	Used With Cable Ties	M, I, S
•	Min. Order UOM	PC
•	Min. Order Qty.	100
	BOM Qty. (# of Pkgs.)	


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY	
PANDUIT WITH RESPECT TO ADHESIVE BOND PERFOMANCE.	
AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH	
THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE	
TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CON	ITROL.



PANDUIT	WEIGHT	USE WITH ANY OF			
PART	bs/100 pcs	THESE CABLE TIE			
NUMBER*	(g)/100 pcs	CROSS-SECTIONS			
ABM100-A	0.26 (119)	M, I, S SG200, SG250, SG300			



ADHESIVE BACKING: RUBBER BASED ADHESIVE PRESSURE
SENSITIVE FOAM TAPE 0.04 [1.0] THICK WITH A PROTECTIVE
LINER. MOUNT IS DESIGNED TO SUPPORT 0.50 lbs (227g) MAX.
WEIGHT ON A CLEAN DRY SMOOTH SURFACE.

## NOTES

- 1. SEE CURRENT PRICE SHEET FOR PART
  NUMBER SUFFIX DESIGNATION FOR
  PACKAGE SIZE AND COLOR.
  2. THE '-A' SUFFIX REPRESENTS RUBBER
  ADHESIVE.
  3. SUPPLIED IN STRIPS OF TWO.

- 4. MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 120°F (49°C).
  5. HOLE FOR STANDARD S6 FLAT HEAD SCREW.

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

									G00033BA_DC_ABM100A_06				
											DUIT corp.	TINLEY PARK, ILLINO	IS
										ABM 100 - A FOUR - WAY MOUNT UNLESS OTHERWISE SPECIFIED.			
										DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ±5*		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECT	CTION.
										DRAWN BY MJK	MAT'L:	SCALE NONE	
6	8-24-05	TMSA		REMOVED PART NUMBER ABM25	GB0033BA	6				12/09/92	NYLON 6/6	GB0033BA	DWG
REV	DATE	BY	снк	DESCRIPTION	ECN -	R	CUST	SUP		СНК'D		ODOCSSDA	SIZE