ABM3H-A-L






- Superior adhesive for long term reliability
 - 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with PANDUIT cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

Part Number	ABM3H-A-L
RoHS Compliancy Status	Compliant
Part Description	4-Way Adhesive Backed Cable Tie Mount
Product Type	Cable Tie Mounts - Adhesive Backed
Material	Nylon 6.6
Color	White
 UL Recognized 	E136577
Height (In.)	.25
Height (mm)	6.4
Length (In.)	1.50
Length (mm)	38.1
Width (In.)	1.50
• Width (mm)	38.1
Adhesive Type	Rubber
 CE Compliant 	CT-ACC1 / 10.96
Environment	Indoors
Max. Bundle Diameter (mm)	8.9
Mounting Method	Adhesive Backed
Pricing Description	Cable Tie Mount, Adh., 1.5"x1.5" (38.1mm x 38.1m
Screw Size	#6 (M3)
Screw Size Metric	M3
Used With Cable Ties	M, I, S, HS, LH, H, HLM
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

NOTES:





SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX

I=INTERMEDIATE,S=STANDARD,LH=LIGHT HEAVY,H=HEAVY.

CABLE TIE CROSS SECTION CODE: M=MINIATURE,

DESIGNATIONS FOR PACKAGE SIZE.

PANDUIT * USE WITH THESE CABLE TIE ** CROSS SECTIONS (9) /100 pcs. ABM3H-A (ABM4O) M, I, S, LH & H (274)

TO APPLY MOUNT

- 1) REMOVE PROTECTIVE LINER.
- 2) PLACE IN DESIRED LOCATION. 3) APPLY PRESSURE TO MOUNT.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS G00239GW_DC_ABM3H - A_02



TINLEY PARK. ILLINOIS

ABM3H-A ADHESIVE BACKED MOUNT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.1(2.5) (.XXX) ±0.020(.5) (.XX) ±0.05(1.3)ANGLES ±5* UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

2	9-20-05	TMSA		REMOVED TOLERANCE FROM REF HOLE DIAMETER OF .146	GB0239GW	2			(.X) ±0. (.XX) ±0.	
1	11/2/04	JAD		ADD ABM40	GB0239GW	1			DRAWN BY CGSM	МА
R	10-20-00	CGSM		INITIAL RELEASE	GB0239GW	R			10-20-00	
REV	DATE	BY	снк	DESCRIPTION	ECN -	R	CUST	SUP	CHK'D	

MOUNT SHOULD NOT BE USED WITH M, I OR S CROSS SECTION CABLE TIES WITH LESS THAN A 2" BUNDLE DIAMETER.

WHITE GB0239GW A