## ABMM-A-C






- Superior adhesive for long term reliability
  - 2-up mount configuration speeds liner removal and installation
  - 4-way cable tie entry makes part orientation fast and easy
  - Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
  - Used with PANDUIT cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

■ Part Number	ABMM-A-C
<ul> <li>RoHS Compliancy Status</li> </ul>	Compliant
■ Part Description	4-Way Adhesive Backed Cable Tie Mount
■ Product Type	Cable Tie Mounts - Adhesive Backed
■ Material	ABS
<b>≖</b> Color	White
■ UL Recognized	E136577
■ Height (In.)	.18
<ul><li>Height (mm)</li></ul>	4.6
- Length (In.)	.75
■ Length (mm)	19.1
■ Width (In.)	.75
■ Width (mm)	19.1
■ Adhesive Type	Rubber
■ CE Compliant	CT-ACC1 / 10.96
■ Environment	Indoors
■ Max. Bundle Diameter (mm)	3.7
<ul> <li>Mounting Method</li> </ul>	Adhesive Backed
<ul> <li>Pricing Description</li> </ul>	Cable Tie Mount, Adh., .75"x.75" (19.1mm x 19.1mm), WH
<ul> <li>Used With Cable Ties</li> </ul>	M, I
■ Min. Order UOM	PC
■ Min. Order Qty.	100
■ BOM Qty. (# of Pkgs.)	

- = = ... =.., . (.. = . . . . . . . . . . . . . . .
- Add to Favorite Product List

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



0.065±0.010 [1.65±.254]

 $0.171 \pm 0.020$ 

[4.34±.508]

ADHESIVE TAPE

GREASE-FREE SURFACE.

0.180

[4.6]

(REF)

PRESSURE SENSITIVE TAPE 0.040(1.0)
THICK WITH PROTECTIVE LINER. MOUNT
IS DESIGNED TO SUPPORT 0.30 | bs(136 g)

MAX. WEIGHT ON A CLEAN, DRY, SMOOTH,

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.


PANDUIT * PART NO. *	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT  bs (g)/100 pcs		
АВММ - А	MINIATURE INTERMEDIATE	0.113 (51.3)		

## TO APPLY MOUNT

- 1) CLEAN SURFACE WITH ISOPROPYL ALCOHOL.
- 2) REMOVE PROTECTIVE LINER.
- 3) PLACE IN DESIRED LOCATION.
- 4) APPLY PRESSURE TO MOUNT FOR 5 SECONDS.



- \* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- 2) MOUNTS ARE SUPPLIED IN STRIPS OF TWO FOR EASY REMOVAL OF LINER.
- 3) MOUNT HAS A CONTINUOUS OPERATING TEMPERATURE OF 120°F(49°C).



## ACTUAL SIZE

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G00239GB\_DC\_ABMM\_A\_09



TINLEY PARK, ILLINOIS

## ABMM-A ADHESIVE BACKED MOUNT

	l la companya di managantan di managantan di managantan di managantan di managantan di managantan di managanta					, (B) (E) 1 (E) (B) (G) (G) (G)							
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X)		UNLESS OTHERWISE SPECIFIED.	
												IN INCHES, THIRD ANGLE PROJECTION.	
										CGSM	MAT'L:	scale NONE	
9	6/29/06	JAD		REMOVE ABM20	GB0239GB	9				1 - 20 - 99	ABS (ACRYLONITRILE BUTADIENE STYRENE)		D₩G
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP		CHK *D		GB0239GB	SIZE