



## CF503850F-Q



- Material: Polypropylene  
Color: Black

Panduit's line of fittings provide a secure way to join CLT at junctions and breakouts while improving the appearance of wire harnesses.

✦ Part Number	CF503850F-Q
✦ RoHS Compliancy Status	Compliant
✦ Part Description	Corrugated Loom Tubing Fittings improve system appearance while protecting wires.
✦ Material	Polypropylene
✦ Color	Black
✦ Length (In.)	2.30
✦ Length (mm)	58.4
✦ Branch Diameter (In.)	.50
✦ Branch Diameter (mm)	12.7
✦ Flammability Rating	UL HB
✦ Pricing Description	CLT Fitting .50" x .38" x .50" (12.7mm x 9.7mm x 12.7mm)
✦ Temperature Range	-40°F to 176°F ( -40°C to 80°C)
✦ Trunk Diameter (In.)	.38
✦ Trunk Diameter (mm)	9.5
✦ Tubing Diameters	.500 x .375 x .500
✦ Min. Order UOM	PC
✦ Min. Order Qty.	25
✦ BOM Qty. (# of Pkgs.)	
✦ Add to Favorite Product List	