T50F-C





- Largest variety of colors materials and sizes in the industry
 - Available in seven different materials and twelve different colors
 - Colors conform to Communications Wiring Standards
 - Flexible, neat, fast
 - Allows breakouts of single/multiple wires and rerouting of replacement wires
 - Harness multiple cables into a single manageable bundle
 - A protection for wires cables hoses and tubing
 - Color code wire bundles
 - Reusable
 - Tool supplied in each package
- *Order number of reels required.
- **Flame retardant products are manufactured from a material that is rated UL94V-0. ‡Reel packaging may contain splices.

■ Part Number	T50F-C
 RoHS Compliancy Status 	Compliant
 Part Description 	Spiral Wrap offers abrasion protection for wires, cables, hoses and tubing
Material	Polyethylene
■ Color	Natural
■ UL Recognized	E141152
■ Bundle Diameter Range (In.)	3/8 to 4
■ Bundle Diameter Range (mm)	9.5 to 101.6
■ Flammability Rating	UL94 HB
■ Length Per Reel (ft.)	100
■ Length Per Reel (m)	30.5
■ Min. Bundle Diameter (In.)	.38
■ Min. Bundle Diameter (mm)	9.5
Outside Diameter (In.)	.50
Outside Diameter (mm)	12.7
 Pricing Description 	Spiral Wrap, .50" (12.7mm) x 100', Poly, Natural
 Temperature Range 	-40°F to 122°F (-40°C to 50°C)
■ Wall Thickness (In.)	.06
■ Wall Thickness (mm)	1.50
■ Wrap Width (In.)	.50
Wrap Width (mm)	12.7
■ Min. Order UOM	RL
■ Min. Order Qty.	1