

TA1S8-C





- Low profile and versatile these screw-installed mounts can be ideal for applications where space is limited. Designed for four-way cable tie insertion this mount can be mounted in-line or perpendicular to the wire bundle.
- 4-way cable tie entry makes part orientation fast and easy
 - Install with a screw or rivet for a strong, secure installation
 - Small overall size allows use where space is limited
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Ties.

Part Number	TA1S8-C
 RoHS Compliancy Status 	Compliant
 Part Description 	Cable Tie Mount - Screw Applied
■ Product Type	Cable Tie Mounts - Screw / Rivet Mounted
Material	Nylon 6.6
■ Color	Natural
■ UL Recognized	E136577
■ Height (In.)	.20
Height (mm)	5.1
- Length (In.)	.75
■ Length (mm)	19.1
■ Width (In.)	.38
■ Width (mm)	9.5
■ CE Compliant	CT-ACC4 / 10.96
■ Environment	Indoors
■ Flammability Rating	UL94 V-2
■ Hole Diameter (In.)	.17
■ Hole Diameter (mm)	4.3
■ Max. Bundle Diameter (mm)	4.8
■ Mounting Method	#8 (M4) Screw
■ Pricing Description	Tie Mount, Tie Anchor, #8 Screw (M4)
■ Screw Size	#8 (M4)
 Screw Size Metric 	M4
Used With Cable Ties	M, I, S
■ Min. Order UOM	PC

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER*	SUFFIX	MATERIAL	"D"	REC. FAST.	WEIGHT bs/100 pcs (g)/100 pcs	USE WITH THESE CABLE TIE CROSS-SECTIONS
TA1S8	NONE -0 -30 -69	NYLON 6/6 WEATHER RESISTANT NYLON HEAT STABILIZED NYLON FLAME RETARDANT NYLON	0.170 (4.3)	#8 (M4) SCREW	0.07 (32.0)	MINIATURE INTERMEDIATE STANDARD
TAIS10	NONE - 0	NYLON 6/6 WEATHER RESISTANT NYLON	0.200	#10 (M5) SCREW	0.07 (32.0)	MINIATURE INTERMEDIATE STANDARD





NOTES:

 SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS GB0239EP_PB_TA1_02

PANDUIT COR

TINLEY PARK, ILLINOIS

TA1 - TIE ANCHOR MOUNT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ±5*

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY MAT'L: DATE 7/9/02 JAD UPDATED .195(4.95) DIMENSION LINE GB0239EP 2 12/17/96 CHK 'D REV DATE BY CHK DESCRIPTION ECN - R CUST SUP

SEE TABLE

SCALE NONE

DRAWING NO.

GB0239EP A
SIZE