




BM1M-C




- For indoor use
- Used to fasten and identify bundles at the same time
- Stainless steel locking barb provides consistent performance, reliability and infinite adjustability through entire bundle range
- Can be marked with *PANDUIT* Marker Pens or custom imprinted with text, symbols or trademarks available using *PANDUIT* Custom Hot Stamping Service
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

| | |
|------------------------------|---|
| Part Number | BM1M-C |
| RoHS Compliancy Status | Compliant |
| Part Description | Marker Tie with metal barb, Wrap, 4.2", Miniature cross section |
| Product Type | Cable Ties |
| Material | Nylon 6.6 |
| Color | Natural |
| CSA Certified | Yes |
| Mil. Std. Part Number | MS3368-5-9E |
| UL Listed (File #E56854) | No |
| UL Recognized (File #E56854) | Yes |
| Length (In.) | 4.2 |
| Length (mm) | 107 |
| Width (In.) | .095 |
| Width (mm) | 2.4 |
| CE Compliant | Yes |
| Cross Section | Miniature |
| Head Height (In.) | .156 |
| Head Height (mm) | 4.0 |
| Head Width (In.) | .182 |
| Head Width (mm) | 4.6 |
| Locking Style | Locking |
| Marker Type | Wrap |
| Marker Write-On Area (In.) | .29 x 1.09 |
| Marker Write-On Area (mm) | 7.4 x 27.7 |
| Material Flammability Rating | UL 94V-2 |

| | |
|-------------------------------------|--|
| ■ Max. Bundle Diameter (In.) | .90 |
| ■ Max. Bundle Diameter (mm) | 23 |
| ■ Max. Continuous Use Temperature | 185°F (85°C) |
| ■ Min. Loop Tensile Strength (Lbs.) | 18 |
| ■ Min. Loop Tensile Strength (N) | 80 |
| ■ Pricing Description | Marker Tie, Wrap, 4.2"L (107mm), Miniature, Nylon, Natural |
| ■ Thickness (In.) | .046 |
| ■ Thickness (mm) | 1.2 |
| ■ Tool | GTS, GTSL, GS2B, PTS, PPTS, STS2 |
| ■ Min. Order UOM | PC |
| ■ Min. Order Qty. | 100 |
| ■ BOM Qty. (# of Pkgs.) | |

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT * PART NUMBER | BUNDLE DIA. | | A in (mm) | B in (mm) | C in (mm) | D in (mm) | E in (mm) | F in (mm) | G in (mm) | H in (mm) | J in (mm) | WRITE-ON AREA in. (mm) | MINIMUM LOOP TENSILE lbs. (N) | CROSS-SECTION | WEIGHT (g) lbs./100 pcs. |
|--------------------------|--------------|--------------|---------------|---------------|---------------|---------------|---------------|--------------|----------------|--------------|--------------|------------------------------|-------------------------------------|---------------|-----------------------------|
| | MIN (mm) | MAX (mm) | | | | | | | | | | | | | |
| BM1M | .18 (4.8) | 0.90 (23) | .046 (1.2) | .095 (2.4) | .125 (3.2) | .156 (4.0) | .182 (4.6) | 4.2 (107) | 1.12 (28.5) | .31 (7.9) | .03 (.8) | .29 × 1.09 (7.4 × 27.7) | 18 (80) | MINIATURE | .09 (40) |
| BM2M | .18 (4.8) | 2.00 (51) | .046 (1.2) | .095 (2.4) | .125 (3.2) | .156 (4.0) | .182 (4.6) | 7.9 (201) | 1.12 (28.5) | .31 (7.9) | .03 (.8) | | 18 (80) | MINIATURE | .15 (69) |

NOTES:

*SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty MARKER TIE
BM SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± --- (.XXX) ± .020 (.5)
(.XX) ± .02 (.5) ANGLES ± ---

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JABO

MAT'L:

SCALE
NONE

DATE
5-30-97

NYLON 6.6

DRAWING NO.

BT-0248

CHK'D
JVL

DWG
A
SIZE

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |
|-----|---------|-----|-----|----------------------|------|---|------|-----|
| 5 | 12/1/04 | ERW | | REWORDED TITLE BLOCK | 0248 | 5 | | |