

World Leader in Network and Electrical Solutions

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING


Printer Friendly

support | locate distributor | about panduit | careers | worldwide

SEARCH Current refinements (click \boxtimes to remove) 🔀 Region 🖟 USA 🛛 Product Family 🕨 One-Hole, Straight Fixed Tongue Lug 🔀 Text Search: 'CX35-36-CY' Your search criteria matched only one product, shown below. For Use with Stranded Copper Code Conductors Made from high strength electrolytic copper to provide premium electrical and mechanical performance Compact design saves space · Wide wire range-taking capability minimizes inventory requirements Inspection window to visually assure full conductor insertion Plated steel set screw provides high strength, durable electrical contact between conductor and connector • UL Listed and CSA Certified for use up to 600 V Part Number: CX35-36-CY **RoHS Compliancy Status:** Compliant CX35-36-CY replaces CX35-36-C Note: Part Description: Copper, single barrel, one-hole, straight tongue (fixed) lug. Product Type: Mechanical Connectors - Lugs CSA Certified: Yes UL Listed: Yes Height (In.): .48 Height (mm): 12.2 Length (In.): 1.02 Length (mm): 25.9 Copper Conductor Size #14 AWG - #6 AWG Range: Stud Hole Size (In.): 3/16 Tongue Width (In.): .38 Collar Length: .38 Current Rating (Amps): 35 Tightening Torque (In-Lbs): 25 Tongue Length: .44 **Tongue Thickness:** .07 Tongue Width (mm): 9.7 Wire Range (mm²): 2.5 - 16

Min. Order UOM: PC Min. Order Qty .: 1 BOM Qty. (# of Pkgs.) Add to My Catalog


			INE 2 -		ANDUIT 1 4			DTE 2	5.F	B. T PANDU RE T	IN PLA	'S T N TED).	VITH A "T		TIFIED	Ista
	PANDUI	т	DIMENSIONS ± .02								MAX	-	MARKINGS				
	PART NUMBR		G \	WK	A	M	T	H	L	E	- AMERA RATI	\GE	LINE 1	LINE	2	HEX SIZE	(MAX)
	CX35-36-(CY	22 .3	38 .19	1.02	.38	.07	.48	.35	.20	35		CX-35	6-1	4	SCREW	.22
	CX35-36T-	CY	22 .3	38 .19	1.02	.38	.07	.48	.35	.20	35		CX-35	6-1	4	SCREW	.22
	CX70-14-(CY .	31 .5	50 .25	5 1.27	.50	.08	.57	.46	.27	70		CX-70	4 - 1	4	SCREW	.28
	CX70-14T-	CY .:	31 .5	50 .25	5 1.27	.50	.08	.57	.46	.27	70		CX-70	4 - 1	4	SCREW	.28
	CX125-14-	QY .	43 .6	52 .31	1.53	.62	.13	77	.57	.27	125	5	CX-125	5 1/0-	· 4	SCREW	. 41
	CX125-56T	-QY _4	43 .6	.31	1.53	.62	.13	77	.57	.34	125	5	CX-125	5 1/0-	· 4	SCREW	. 41
	CX225-56-	QY .	56 1.	00 .50	2.19	1.00	.13	1.13	.85	.34	225	5	CX-225	5 4/0-	·2	9/16	.50
	CX225-56T	-QY .5	56 1.	00 .50	2.19	1.00	.13	1.13	.85	.34	225	5	CX-225	5 4/0-	·2	9/16	.50
	CX225-38T	-QY .s	56 1.	00 .50	2.19	1.00	.13	1.13	.85	.38	225	5	CX-225	5 4/0-	2	9/16	.50
	CX400-38-	3Y .8	88 1.	50.75	5 3.16	1.38	.19	1.65	1.13	.44	400)	CX-400	500kcmi	-4/0	3/4	.81
	*CX400-12T	-3Y .8	88 1.	50 .75	3.16	1.38	.19	1.65	1.13	.50	400)	CX-400	500kcmi	-4/0	3/4	.81
	* PART IS	5 NOT	UL OR	CSA C	ERTIFIE	ED											C41664
																ΤI	NLEY PARK, ILLINO
00 3	3/06 JHNULEM	LEM DRAWING RELEASED - ROHS COMPLIANT						PC003	348			"CX" SERIES COPPER MECHANICAL LUGS					
REV [REV DATE BY CHK DESCRIPTION						ECN	# CI	JST PM	DRAV	AWN BY CH	ΗK [•] D	SCALE NO		AWING NO. C41664		







K



2. SLOTTED HEAD SCREW USED IF HEX SIZE IS NOT GIVEN.

NOTES:

 PM	drawn by JHNU	CHK D	SCALE NC	NE
	"CX"	SERIES	COPPER	MEC

- FOR CX70-14-C ARE:
- 3. PACKAGE QTY. -Q=25 -C = 1004. ADDITIONAL MULTIPLE WIRE COMBINATIONS
- UL LISTED AND CSA CERTIFIED FOR: A. 600V MAX. VOLTAGE RATING. B. AMPERAGE LISTED IN TABLE.
- THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

