

World Leader in Network and Electrical Solutions

support | locate distributor | about panduit | careers | worldwide

Printer Friendly

	(click ⊠ to remove)	Search Ti	
🗙 Region 🕨 USA 🔀 Pro	duct Family I Code Conductor, One-Hole, Standard Barrel with Window Lug ⊠ Text S		
	Your search criteria matched only one product, shown below.	Related Products Contour Crimp [™] Control	
	For Use with Stranded Copper Conductors	Die Type, Manual, Crimping Tool	
C. C. C.	 Color-coded barrels marked with <i>PANDUIT</i> and specified competitor index numbers for proper crimp die selection Inspection window to visually assure full conductor insertion Tin-plated to inhibit corrosion UL Listed and CSA Certified to 35 KV** and temperature rated to 9 when crimped with <i>PANDUIT</i> and specified competitor crimping tools dies UL Listed and CSA Certified for wide wire range-taking capability w crimped with <i>PANDUIT</i>® <i>Uni-Die</i>™ Dieless Crimping Tools‡ Tested by Telcordia – meets NEBS Level 3 American Bureau of Shipping Approved 	Die Type, Nandal Hydraulic, 14 Die Type, Remote Hydraulic, 14 Die Type, Battery Powered Hydra 0°C s and	
Part Number:	LCA2-14-Q		
RoHS Compliancy Status:	Compliant		
Part Description:	One-hole, standard barrel with window lug, #2 AWG wire, 1/4" stud hole.		
Product Type:	Compression Connectors - Lugs		
CSA Certified:	Yes		
UL Listed:	Yes		
Length (In.):	1.77		
Length (mm):	45.0		
Copper Conductor Size:	#2 AWG		
Stud Hole Size (In.):	1/4		
Tongue Width (In.):	.60		
Barrel Length (In.):	.88		
Angle:	Straight		
Clearance:	.38		
Figure No.:	1		
Mechanical:	CT-1700***		
Panduit Color Code:	Brown		
Panduit Die Index No.:	P33		
Tongue Thickness:	.10		
Tongue Type:	Standard		
Tongue Width (mm):	15.2		
Wire Range (mm ²):	35		
Wire Strip Length (In.):	15/16		
Min. Order UOM:	PC		
Min. Order Qty.:	1		
Burndy Die Index No.:	10		
T&B Die Index No.:	33		

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

RELEASED

DESCRIPTION

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	2 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	15/16 in.
Stud Size	1/4 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90 ° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P33
Alternate Industry Die Index No. () on Barrel	(10)



9/02

DATE


00

REV

SAB DRL

BY CHK

LISTED Wire Connector



ECN

N/A

LCA2-14-CUST