World Leader in Network and Electrical Solutions

Printer Friendly

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

SEARCH

Current refinements (click **x** to remove)

Search Tips 🍘

🔣 Region 🕽 USA 🔃 Product Family 🕽 Code Conductor, One-Hole, Standard Barrel with Window Lug 🔀 Text Search: 'LCA8-10-L'



BOM Qty. (# of Pkgs.)

For Use with Stranded Copper Conductors

- Color-coded barrels marked with PANDUIT and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with PANDUIT and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range-taking capability when crimped with *PANDUIT*® *Uni-Die*[™] Dieless Crimping Tools‡
- Tested by Telcordia meets NEBS Level 3
- American Bureau of Shipping Approved

| - 126 | NI OF | Od. | Proc | 11101 |
|-------|-------|-----|------|-------|
| 17.6 | สเสเ | CU | ГІО | เนษเ |

Contour Crimp™ Control...

Die Type, Manual, Crimping Tool

CD-720 Crimping Dies

Die Type, Manual Hydraulic, 14 Ton,...


Die Type, Remote Hydraulic, 14 Ton,...


Die Type, Battery Powered Hydraulic...

More...

| Part Number: | LCA8-10-L | | | |
|----------------------------|--|--|--|--|
| RoHS Compliancy Status: | Compliant | | | |
| Part Description: | One-hole, standard barrel with window lug, #8 AWG wire, #10 stud hole. | | | |
| Product Type: | Compression Connectors - Lugs | | | |
| CSA Certified: | Yes | | | |
| UL Listed: | Yes | | | |
| Length (In.): | 1.25 | | | |
| Length (mm): | 31.8 | | | |
| Copper Conductor Size: | #8 AWG | | | |
| Stud Hole Size (In.): | #10 | | | |
| Tongue Width (In.): | .41 | | | |
| Barrel Length (In.): | .56 | | | |
| Angle: | Straight | | | |
| Clearance: | .31 | | | |
| Figure No.: | 1 | | | |
| Mechanical: | CT-1700*** CT-720 CT-1570 CT-1701 CT-100 CT-200 | | | |
| Panduit Color Code: | Red | | | |
| Panduit Die Index No.: | P21 | | | |
| Tongue Thickness: | .08 | | | |
| Tongue Type: | Standard | | | |
| Tongue Width (mm): | 10.4 | | | |
| Wire Range (mm²): | 10 | | | |
| Wire Strip Length (In.): | 5/8 | | | |
| Min. Order UOM: | PC | | | |
| Min. Order Qty.: | 1 | | | |
| Burndy Die Index No.: | 49 | | | |
| T&B Die Index No.: | 21 | | | |
| | | | | |

| Material | High Conductivity Seamless Copper Tube | | |
|---|--|--|--|
| Plating | Electro-Tin | | |
| Wire Size | 8 AWG | | |
| Wire Type | Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric | | |
| Wire Strip Length | 5/8 in. | | |
| Stud Size | #10 | | |
| UL Listed Wire Connector | Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts. | | |
| UL Temperature Rating | 90°C | | |
| C.S.A Certified Wire Connector | Yes | | |
| Panduit Color Code on Barrel | RED | | |
| Panduit Die Index No. on Barrel | P21 | | |
| Alternate Industry Die Index No. () on Barrel | N/A | | |









| | | | | | | CORP. TINLEY PARK, ILLINOIS |
|-----|------|-----|-----|-------------|-------|--|
| | | | | | | LCA8-10-L |
| 00 | 9/02 | SAB | DRL | RELEASED | 10318 | Copper Lug - One-Hole, Standard Barrel |
| REV | DATE | BY | снк | DESCRIPTION | ECN | SCALE DRAWING NO / CAD FILE LCA8-10-CUST |