World Leader in Network and Electrical Solutions

Printer Friendly

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

SEARCH

Current refinements (click **x** to remove)





For Use with Stranded Copper Conductors

🗵 Region 🕽 USA 🔀 Product Family 🕽 Code Conductor, One-Hole, Standard Barrel with Window Lug 🔀 Text Search: 'LCA8-14-L'

- Color-coded barrels marked with PANDUIT and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with PANDUIT and specified competitor crimping tools and
- UL Listed and CSA Certified for wide wire range-taking capability when crimped with *PANDUIT*® *Uni-Die*™ Dieless Crimping Tools‡
- Tested by Telcordia meets NEBS Level 3
- American Bureau of Shipping Approved

Related Product			
	2100	Droc	

Contour Crimp™ Control...

Die Type, Manual, Crimping Tool

CD-720 Crimping Dies

Die Type, Manual Hydraulic, 14 Ton,...


Die Type, Remote Hydraulic, 14 Ton,...


Die Type, Battery Powered Hydraulic...

D. (N. ol.)	1010441
Part Number:	LCA8-14-L
RoHS Compliancy Status:	Compliant
Part Description:	One-hole, standard barrel with window lug, #8 AWG wire, 1/4" stud hole.
Product Type:	Compression Connectors - Lugs
CSA Certified:	Yes
UL Listed:	Yes
Length (In.):	1.34
Length (mm):	34.0
Copper Conductor Size:	#8 AWG
Stud Hole Size (In.):	1/4
Tongue Width (In.):	.48
Barrel Length (In.):	.56
Angle:	Straight
Clearance:	.37
Figure No.:	1
Panduit Color Code:	Red
Panduit Die Index No.:	P21
Tongue Thickness:	.07
Tongue Type:	Standard
Tongue Width (mm):	12.2
Wire Range (mm²):	10
Wire Strip Length (In.):	5/8
Min. Order UOM:	PC
Min. Order Qty.:	1
Burndy Die Index No.:	49
T&B Die Index No.:	21
BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON	A RESTRICTED BASIS AND IS NOT TO BE U	JSED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.
Material	High Conductivity	

Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	8 AWG		
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		
Wire Strip Length	5/8 in.		
Stud Size	1/4 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90°C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	RED		
Panduit Die Index No. on Barrel	P21		
Alternate Industry Die Index No. () on Barrel	N/A		









						CORP. TINLEY PARK, ILLINOI
						LCA8-14-L
00	9/02	SAB	DRL	RELEASED	10318	Copper Lug - One-Hole, Standard Barrel
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCA8-14-CUST