Contour Crimp™ Control...

CD-2001 Crimping Dies

Die Type, Battery Powered Hydraulic... Die Type, Battery Powered Hydraulic...

Die Type, Manual Hydraulic, 14 Ton,...

Die Type, Remote Hydraulic, 14 Ton,...

## World Leader in Network and Electrical Solutions


**Printer Friendly** 

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

**SEARCH** 

Current refinements (click **x** to remove)

Search Tips 7





For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV\*\* and temperature rated to 90°C when crimped with PANDUIT and specified competitor crimping tools and dies
- American Bureau of Shipping Approved

Part Number:	LCAX1-38-X
RoHS Compliancy Status:	Compliant
Part Description:	Flex Lug, #1 AWG, 3/8" Stud Hole
Length (In.):	1.80
Length (mm):	45.7
Class G,H, I, K, M:	#1 AWG
Diesel Locomotive:	#1 AWG
Stud Hole Size (In.):	3/8
Tongue Width (In.):	.76
Barrel Length (In.):	.66
Angle:	Straight
Figure No.:	1
Panduit Color Code:	Green
Panduit Die Index No.:	P37
Tongue Thickness:	.12
Tongue Type:	Standard
Tongue Width (mm):	19.3
Wire Strip Length (In.):	3/4
Min. Order UOM:	PC
Min. Order Qty.:	1
Burndy Die Index No.:	11
T&B Die Index No.:	37
BOM Qty. (# of Pkgs.)	
A LLC M. October	

Add to My Catalog

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.


## THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


Material	High Conductivity Seamless Copper Tube			
Plating	Electro-Tin			
Wire Size	1 STR/FLEX			
Wire Type	Stranded Copper: Class B & C, Compact, Class G, H, I, K, M, Locomotive			
Wire Strip Length	3/4 in.			
Stud Size	3/8 in.			
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.			
UL Temperature Rating	90°C			
C.S.A Certified Wire Connector	Yes			
Panduit Color Code on Barrel	GREEN			
Panduit Die Index No. on Barrel	P37			
Alternate Industry Die Index No. ( ) on Barrel	(11)			





LISTED Wire Connector





						PANDUIT CORP. TINLEY PARK, ILLINOIS
						LCAX1-38-X
00	6/03	CJM	SAC	RELEASED	10850	Copper Lug - One-Hole, Standard Flex Barrel
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCAX1-38-CUST