PANDUIT

G2X4WH6-A



• Choose from 36 sizes of *PANDUIT®* Type G Wiring Duct from 0.5 "x 0.5" up to 6" x 4" in popular colors. Used for general purpose control panel wiring and to route and protect wiring in communication closets. The non-slip cover conceals all wiring and is easy to install. The duct and cover form a flush sidewall providing increased capacity and improved aesthetics.

Specifications


- Made of lead-free PVC
- UL Recognized continuous use temperature: 122 °F (50°C)
- UL94 Flammability Rating of V-0
- Conforms with NFPA 79-2002 section 14.3.1 requirement for flame retardant material
- Provided with mounting holes

Features and Benefits

- Wide finger/slot design provides greater sidewall rigidity and can be used with a wide range of wire bundle sizes
- PANDUIT® exclusive rounded edges protects hands and wiring/cabling from abrasion
- Non-slip cover stays in place during shipment, vibration and when in vertical orientation, eliminating rework
- Flush cover design holds 10-12% more wires than traditional duct designs
- Double scoreline allows quick modification for larger cabling bundles saving installation time leading to a lower installed cost
- Specially formulated lead-free material eliminates health concerns associated with PVC that contains lead
- Restricted slot design retains wire in slot for fast, easy wire installation or removal
- Base and cover sold separately.

| ■ Part Number | G2X4WH6-A |
|--|---------------------------------------|
| ■ RoHS Compliancy Status | Compliant |
| ■ Part Description | Wide finger, slotted wiring duct. |
| ■ Material | Lead-Free PVC |
| ■ Color | White |
| ■ CSA Certified | Yes |
| ■ UL Recognized (File No. E147128) | Yes |
| ■ Length (ft.) | 6 |
| Adhesive Mounting Tape | Yes |
| CE Marking | Yes |
| ■ Duct Size W x H (In.) | 2.25 x 4.10 |
| ■ Duct Size W x H (mm) | 57.2 x 104.1 |
| Mounting Method | Standard Mounting Holes with Adhesive |
| ■ Pricing Description | Slotted Duct, PVC,2"X4"X6',ADH,WHT |

| ■ Slot Width (In.) | 0.31 |
|----------------------------------|-------|
| ■ Slot Width (mm) | 7.9 |
| ■ Cover Part Number | C2WH6 |
| Min. Order UOM | FT |
| ■ Min. Order Qty. | 6 |
| ■ BOM Qty. (# of Pkgs.) | |



- 1. ALL DIMENSIONS ARE REFERENCE ONLY.
- 2. DIMENSIONS IN PARENTHESIS ARE METRIC.
- 3. THE * * DENOTE COLOR.
- 4. DUCT AND COVER ARE AVAILABLE IN 6 FT [1828.8] LENGTHS.

| | | | | | CAD FILENAME/LAYER | CAD FILENAME/LAYERS D11000QT_DC_00C | | | |
|-----|--------|------|------|---|--------------------|---|--------------------------|------|--|
| | | | | G. ADDED LENGTH NOTE F. CORRECTED DIMENSIONS | PAN | | DRP. TINLEY PARK, ILLINO | ıIS | |
| 2 | 7/6/07 | JCST | MKBE | E. DELETED DIMENSION D. ADDED DIMENSION | WIRING | WIRING DUCT - TYPE G DUCT WITH COVER 2 X 4 | | | |
| | | | | C. CHANGED DRAWING SIZE | | MARKETING DRAWING | | | |
| 1 | 5/6/04 | JCST | MKBE | B. CHANGED VIEW A. ADDED TOP VIEW, LABELS, AND NOTES | DRAWN BY JCST | MAT'L: | SCALE FULL | | |
| R | 3/6/03 | JCST | JGG | DRAWING RELEASED | DATE 3/6/03 | PVC | DRAWING NO. | DWG | |
| REV | DATE | ВҮ | СНК | DESCRIPTION | CHECKED BY JGG | | 36897-707 | SIZE | |