H1.5X2WH6






Type H Wiring Duct is ideal for applications that require easy access in control panels and communication closets for frequent equipment modifications or repairs where moves, adds and changes are common. Due to the hinging feature, Hinged Cover Slotted Wall Wiring Duct reduces the time and hassle associated with removing and reinstalling traditional duct cover to perform maintenance or changes.

- Specifications
 - Made of lead-free PVC
 - Rated for continuous use temperature: 122°F (50°C)
 - UL94 Flammability Rating V-0
 - Conforms with NFPA 79-2007 section 13.3.1 requirement for flame retardant material
 - Available in Black, Light Gray and White
 - Provided with standard mounting holes
 - * Height dimension includes duct with cover
- Features and Benefits
 - Integrated hinged cover design allows easy access to wiring without hassle of removing and reinstalling cover
 - Dual-sided hinge can open up to 100° from either sidewall of duct base for easy access to channel
 - Cover retention flanges allows the cover to open and close easily
- Double scoreline allows fingers and complete sidewall removal
- Cover removal rib makes cover easy to open from either side
- Restricted slot design retains wire in slot for fast, easy wire installation or removal
- Base and cover sold separately.

 Part Number 	H1.5X2WH6
 RoHS Compliancy Status 	Compliant
 Part Description 	Wide finger, slotted hinged wiring duct.
 Material 	Lead–Free PVC
▪ Color	White
 CSA Certified 	Yes
 UL Recognized (File No. E147128) 	Yes
■ Length (ft.)	6
 Duct Size W x H (In.) 	1.75 x 1.98
 Duct Size W x H (mm) 	44.5 x 50.3
 Mounting Method 	Standard Mounting Holes
 Pricing Description 	Slotted Hinged Duct, PVC, 1.5"X2"X6', White
 Cover Part Number 	HC1.5WH6
 Min. Order UOM 	FT
 Min. Order Qty. 	6

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTE.

1. ALL DIMENSIONS ARE REFERENCE ONLY.

2. DIMENSIONS IN PARENTHESES ARE METRIC.

3. THE * * DENOTE COLOR.

4. USE HC1.5**6 WITH 1.5" WIDE TYPE H DUCT.				*6 WITH 1.5" WIDE TYPE H DUCT.	D110000U_DC_00B				
					PANDUIT CORP. TINLEY PARK, ILLINOIS				
					WIRING DUCT - TYPE HC COVER				
					l.5 Marketing Drawing				
1	8/22/07	JCS1	мкве	A. CORRECTED DIMENSION - WAS 1.88	DRAWN BY JCST	MAT'L;			
R	1/14/05	JCS1	мкве	DRAWING RELEASED	date 1/14/05	PVC	drawing no. 36897 - 1031	Dwg	
REV	DATE	BY	СНК	DESCRIPTION	снк о МКВЕ			SIZE	