PANDUIT *

H3X4WH6



Type H Wiring Duct is ideal for applications that require easy access in control panels and communication closets for frequent equipment modifications or repairs where moves, adds and changes are common. Due to the hinging feature, Hinged Cover Slotted Wall Wiring Duct reduces the time and hassle associated with removing and reinstalling traditional duct cover to perform maintenance or changes.

Specifications

- Made of lead-free PVC
- Rated for continuous use temperature: 122°F (50°C)
- UL94 Flammability Rating V-0
- Conforms with NFPA 79-2007 section 13.3.1 requirement for flame retardant material
- Available in Black, Light Gray and White
- Provided with standard mounting holes
- * Height dimension includes duct with cover

Features and Benefits

- Integrated hinged cover design allows easy access to wiring without hassle of removing and reinstalling cover
- Dual-sided hinge can open up to 100° from either sidewall of duct base for easy access to channel
- Cover retention flanges allows the cover to open and close easily
- Double scoreline allows fingers and complete sidewall removal
- Cover removal rib makes cover easy to open from either side
- Restricted slot design retains wire in slot for fast, easy wire installation or removal
- Base and cover sold separately.

■ Part Number	H3X4WH6
 RoHS Compliancy Status 	Compliant
■ Part Description	Wide finger, slotted hinged wiring duct.
■ Material	Lead-Free PVC
≖ Color	White
■ CSA Certified	Yes
■ UL Recognized (File No. E147128)	Yes
■ Length (ft.)	6
■ Duct Size W x H (In.)	3.25 x 4.10
■ Duct Size W x H (mm)	82.6 x 104.1
Mounting Method	Standard Mounting Holes
■ Pricing Description	Slotted Hinged Duct,PVC,3"X4"X6',White
■ Cover Part Number	HC3WH6
■ Min. Order UOM	FT
■ Min. Order Qty.	6

