

## SD2H6



- The wiring duct divider wall is mounted inside any PVC wiring duct in order to create multiple channels within the wiring duct. Simply use the mounting bases when installing the duct and the divider wall will "snap" on.
- Wiring duct divider wall can be mounted inside any type of Panduit® PVC wiring duct to create multiple channels

• Simply install the divider wall base when mounting the duct and snap the divider wall onto the mounting base, DB-C

- All versions snap onto DB-C mounting base
- Divider wall heights 2" and greater have a scoreline feature allowing sections to be removed leaving a smooth edge

• Meets UL508/508A insulation material requirement for barrier between conductors

• UL 94 flammability rating of V-0

<ul> <li>Part Number</li> </ul>	SD2H6
<ul> <li>RoHS Compliancy Status</li> </ul>	Compliant
<ul> <li>Part Description</li> </ul>	Slotted divider wall.
<ul> <li>Material</li> </ul>	Lead-free PVC
■ Color	Light Gray
<ul> <li>Length (ft.)</li> </ul>	6
<ul> <li>For Nominal Duct Height (In.)</li> </ul>	2.00
<ul> <li>For Nominal Duct Height (mm)</li> </ul>	50
<ul> <li>Pricing Description</li> </ul>	SLOTTED DUCT DIVIDER WALL, PVC, 2"H X 6'
<ul> <li>Min. Order UOM</li> </ul>	FT
<ul> <li>Min. Order Qty.</li> </ul>	6
DOM Other (# of Direct)	

BOM Qty. (# of Pkgs.)

	THIS C	OPY	IS PR	OVIDED ON A RESTRICTED	BASIS AND IS	NOT TO	BE U	SED I	N ANY	WAY DETRIM	ENTAL	TO THE INTERESTS	OF PANDUIT CORP.	_
$\land$		NDU	T P/	ΎΝ "Χ"	"T"			"R"		"F		"G"	WEIGHT	
		SD2H6 1.79 ±.03 (45.3 ±.8)			.07 ±.01 (1.7 ±.3)				1.18 ± (29.9		.8 ±.04 (2.0 ±1.0)			
		SD	3H6	2.74 ±.05 (69.7 ±1.3)	.09 ±.02 (2.1 ±.4)		.26 (6.5	±.C	3 7)	2.11 ± (55.4		1.0 ±.04 (25.4 ±1.0		
		SD	4H6	3.53 ±0.06 (89.8 ±1.5)							:.03 :.8)	1.0 ±.04 (25.4 ±1.0		
	"T" "X" "X" "R" .06 "X" .06 "X" .75 [19.1] .06 .06 .06 .06 .06 .06 .06 .06 .06 .06					[7.9]				3. DIMENSIONS IN PARENTHESES ARE METRIC.				AND
													DC_SDW_02A.prt	
										/			RP. TINLEY PARK, ILLING	DIS
												TTED DIVIDE) DUCT (SD2H6) CUSTOME	ER WALL FOR 8, SD3H6, SD4 r drawing	H6)
										DIME (.X)	NSIONAL ±	RWISE SPECIFIED, TOLERANCES ARE: (.XXX) ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN	
	4/12/01			C. MODIFIED TITLE			1 1 7 144	111111		1 / 77	1 + 031	.8) ANGLES ±	IN INCHES, THIRD ANGLE PROJ	FOTION
2	4/12/04			B. MODIFIED CHART		6089-07				DRAWN BY	ма		504 F	ECTION.
2 1 R	4/12/04 12-10-98 7-23-97	DW			TE 2. 3	6089-07 6089-07 6089-07	нім	HIW HIW HIW			N MA			DWG