## SD4H6





- The wiring duct divider wall is mounted inside any PVC wiring duct in order to create multiple channels within the wiring duct. Simply use the mounting bases when installing the duct and the divider wall will "snap" on.
- Wiring duct divider wall can be mounted inside any type of Panduit® PVC wiring duct to create multiple channels
  - Simply install the divider wall base when mounting the duct and snap the divider wall onto the mounting base, DB-C
  - All versions snap onto DB-C mounting base
  - Divider wall heights 2" and greater have a scoreline feature allowing sections to be removed leaving a smooth edge
  - Meets UL508/508A insulation material requirement for barrier between conductors
  - UL 94 flammability rating of V-0

■ Part Number	SD4H6
<ul> <li>RoHS Compliancy Status</li> </ul>	Compliant
■ Part Description	Slotted divider wall.
■ Material	Lead-free PVC
<b>≖</b> Color	Light Gray
■ Length (ft.)	6
■ For Nominal Duct Height (In.)	4.00
■ For Nominal Duct Height (mm)	100
■ Pricing Description	SLOTTED DUCT DIVIDER WALL, PVC, 4"H X 6"
■ Min. Order UOM	FT
Min. Order Qty.	6
■ BOM Qty. (# of Pkgs.)	



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

36089-07 HIW

|36089-07| HIW

36089-07 HIW

**ECN** 

CHK

HIW


HIW

HIW

CUST

SUP

PAI	NDUIT P/N	"×"	"T"	"R"	"F"	"G"	WEIGHT
	SD2H6	1.79 ±.03 (45.3 ±.8)	.07 ±.01 (1.7 ±.3)	.24 ±.03 (6.0 ±.7)	1.18 ±.03 (29.9 ±.8)	.8 ±.04 (2.0 ±1.0)	.077 LB/FT (.115 Kg/M)
	SD3H6	2.74 ±.05 (69.7 ±1.3)	.09 ±.02 (2.1 ±.4)	.26 ±.03 (6.5 ±.7)	2.11 ±.03 (55.4 ±.8)	1.0 ±.04 (25.4 ±1.0)	.132 LB/FT (.197 Kg/M)
	SD4H6	3.53 ±0.06 (89.8 ±1.5)	.11 ±.02 (2.8 ±.5)	.26 ±.03 (6.5 ±.7)	2.90 ±.03 (73.7 ±.8)	1.0 ±.04 (25.4 ±1.0)	.288 LB/FT (.429 Kg/M)



C. MODIFIED TITLE B. MODIFIED CHART MODIFIED TITLE

A. ADDED DBM-C TO NOTE 2.

DESCRIPTION

RELEASED TO PRODUCTION.

2 4/12/04 JCST

12-10-98

7-23-97

DATE

1

R

REV

JKG

HIW

DW

DW HIW

BY CHK

B

## NOTES:

CAD FILENAME/LAYERS

DATE

- 1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- /A\2. THIS PART IS INTENDED TO BE USED WITH MOUNTING BASE DB-C OR DBM-C IN ORDER TO SUCCEED AS A DIVIDER WALL APPLICATION.
  - 3. DIMENSIONS IN PARENTHESES ARE METRIC.

CORP. TINLEY PARK, ILLINOIS SLOTTED DIVIDER WALL FOR WIRING DUCT (SD2H6, SD3H6, SD4H6) CUSTOMER DRAWING UNLESS OTHERWISE SPECIFIED. UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: ALL DIMENSIONS ARE GIVEN (.XXX) ± IN INCHES, THIRD ANGLE PROJECTION. (.XX) ±.03(.8) ANGLES ±

D36089BG\_DC\_SDW\_02A.prt

SCALE MAT'L: NONE DW DRAWING NO. **PVC** 7-23-97 36089-07 CHECKED BY HIW

DWG

Α

SIZE