

PCSH-B-CR




- Black neoprene sleeving slips on Pan-Steel ™Stainless Steel Ties and custom length banding and is used on applications requiring improved gripping on non-resilient objects, separation between dissimilar metals, and added bundle protection. Can be used indoors or outdoors (excellent ultraviolet resistance, good resistance to petroleum, and many chemicals). Provides full separation between the ties and the material to which you are fastening.
- Operating temperature range 41°F 200°F (5°C 93°C)
 - Supplied in 100 ft (30.5m) reels
 - "C" shaped channel design available in types PCSS-B-CR and PCSH-B-CR cushion sleeve
 - "U" shaped channel design available in type PCSSH-B-CR cushion sleeve

■ Part Number	PCSH-B-CR
■ RoHS Compliancy Status	Compliant
■ Part Description	Cushion sleeving used with heavy cross section ties or custom length banding system, "C" shaped channel design.
■ Color	black
■ Length (ft.)	100
- Length (m)	30.5
■ Width (In.)	.47
■ Width (mm)	11.9
■ Pricing Description	Cushion Sleeving, Heavy, 100ft (30.5m) x .47" (11.9mm) Wd
■ Min. Order UOM	RL
■ Min. Order Qty.	1
■ BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- 1. MAT'L. NEOPRENE
- 2. FLAMMABILITY RATING UL94V-0
- 3. COLOR BLACK
- 4. MATERIAL TO BE SUPPLIED IN 100' LENGTHS
- 5. WGT./100' 3.0 LBS.
- DIM'S IN () ARE mm



S41015_02

								PANDUIT CORP. TINLEY PARK, ILLINOIS			
								PROTECTIVE CUSHION STRIP (HEAVY) PCSH-B-CR			
								DIMENSIONAL TOLERANCES ARE: (XX 2		UNLESS OTHERWISE SPECIFIED,	
02	2/01	KMD		REDRAWN ON CAD						IN INCHES, THIRD ANGLE PROJE	ZCT10N.
01	9/96	JKD	JD	ADDED NOTE 6. ADDED mm TO DIMS.	05048		LA RLS	DRAWN BY MG	MAT'L:	SCALE 10 # 1	
R	3/84	MG	LA	RELEASED		JJ\	LA	DATE 3/15/84	NOTED	DRAFING NO.	D#G
REV	DATE	BY	СНК	DESCRIPTION	ECN .	PM	CUST	JAC		S41015	SIZE