	ធ		support locate distributor	about panduit careers worldwide
	JUIT	World Leader in Network a	nd Electrical Solu	rtions Printer Friendly
	ESOURCES	\mid products \mid services \mid learning	SEARCH	
Current refinements	(click 🔀 to r	remove)		Search Tips 🕜
🔀 Region 🕨 USA 🛛 Pro	oduct Family	▶ Butt Splice, Nylon Insulated 🔀 Text Search: 'BSI		
		Your search criteria matched only one p	roduct, shown below.	
		 Designed to splice two solid or stranded Butted configuration provides low profil Brazed seam protects terminal barrel fr Internal wire stop assures proper length UL Flammability UL 94V-2/HB, maximu UL and CSA rated up to 600 V per UL 4 	le for limited space applications rom splitting during the crimp proces h of insertion into terminal barrel um insulation temperature 221°F (10	SS
Part Number:	BSN18-C			
RoHS Compliancy Status:	Compliant			
Part Description:	Butt Splice 2	22 – 18 AWG, nylon insulated.		
Product Type:	Splices			
CSA Certified:	Yes			
UL Listed:	Yes			
Length (In.):	1.15			
Angle:	straight			
Max. Ins.:	.115			
Panduit Color Code:	Red			
Tool:	CT-100A, CT	T-600-A, CT-1550, CT-1551, CT-2500		
Wire Range:	22 – 18 AWO	3		
Wire Range (mm ²):	0.5 – 1.0			
Min. Order UOM:	PC			
Min. Order Qty .:	100			
BOM Qty. (# of Pkgs.)				
Add to My Catalog				

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.