## World Leader in Network and Electrical Solutions

Printer Friendly

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

**SEARCH** 

Current refinements (click 

to remove)

Search Tips 👩

Your search criteria matched only one product, shown below.

- Designed to splice two solid or stranded wires together to repair or lengthen wires
- Butted configuration provides low profile for limited space applications
- Brazed seam protects terminal barrel from splitting during the crimp process
- Internal wire stop assures proper length of insertion into terminal barrel
- UL Flammability UL 94V-2/HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600 V per UL 486



Add to My Catalog


Part Number: BSN22-C **RoHS Compliancy** Compliant Status: Part Description: Butt Splice 26 - 22 AWG, nylon insulated. Product Type: Splices **CSA Certified:** No UL Listed: No Length (In.): .79 Angle: straight Max. Ins.: .080 Panduit Color Code: Yellow CT-100A, CT-1525, CT-2500 Tool: Wire Range: 26 - 22 AWG 0.14 - 0.5Wire Range (mm²): РС Min. Order UOM: Min. Order Qty.: 100 BOM Qty. (# of Pkgs.)

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT	WIRE SIZE	DIMENSIONS in.					
PART NUMBER		±.03 A	±.01 B DIA.	±.01 C DIA.	±.03		
BSN22	26-22	.79 (20.1)	.08 (2.0)	.04 (1.0)	.47 (1.2)		





## NOTES:

- RATED FOR:
  - A. #26-22 AWG SOLID OR STRANDED COPPER WIRE
  - B. 221° F (105° C) MAX. TEMP. RATING
- 2. MATERIAL:

REV DATE BY

СНК

- A. .02 (0.5) THK COPPER, TIN PLATED
- B. HOUSING NYLON, YELLOW
- PACKAGE QTY: STD. PKG.-C=100 BULK PKG.-M=1000
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS

DESCRIPTION

- INSTALLATION TOOLS: CT-520
- WIRE STRIP LENGTH: 1/4 +1/32

A41337\_04

N/A

DRAWING NO. A41337

04	10/05	RT	LA	REMOVED UL & CSA NOTE	TR00036		TANDUL CORP. TINLEY PARK, ILLINOIS	
03	1/01	RM		FILESPEC WAS N41337AA_PCD_02			#26-22 BARREL NYLON INSULATED BUTT SPLICE	
02	7/95	мС		UPDATED NOTES AND DIMENSIONS	03438			

ECN #

DRAWN BY