

## **CT-1525**



- Specifically designed for the installation of Pan-Term® terminals, disconnects, and splices
- Controlled cycle mechanism assures high quality, consistent terminations
- Ergonomic tool design assures operator comfort, safety, and performance
- Polypropylene handles provide chemical resistance and a cushioned, non-slip grip
- Multiple position locator facilitates a high quality repeatable crimp

- Part Number
- RoHS Compliancy Status
- Part Description

## Product Type

- CE Compliant
- CE Marking
- Pricing Description
- Wire Range (mm<sup>2</sup>)
- Min. Order UOM
- Min. Order Qty.
- BOM Qty. (# of Pkgs.)

## CT-1525

RoHS directive is not applicable

Crimps PANDUIT #26 – #22 AWG insulated terminals and splices, #22 - #10 AWG fully insulated disconnects and insulated parallel splices. Crimps PANDUIT #22 – #14 AWG barrel insulated disconnects.

Crimping Tool

No

## No

Crimp Tool, controlled cycle, crimps PANDUIT insulated terminals, disconnects, and splices  $0.50-6.0\,$ 

PC

1

