World Leader in Network and Electrical Solutions

Printer Friendly

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

SEARCH

Current refinements (click x to remove)

Search Tips 👩

⊠ Region > USA ☑ Product Family > Male Disconnect, Nylon Barrel Insulated – Funnel Entry ☑ Text Search: 'DNF14-250M-C'

Your search criteria matched only one product, shown below.

• Male tab couples with (all .250 x .032) female disconnects

- Male tab can be inserted and removed from the female disconnect without the use of tools for lower installed cost
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Maximum insulation temperature 221°F (105°C)

Related Products

Female Disconnect, Nylon Barrel Ins.. Contour Crimp™ Control...

Wire and Cable Stripping Tools



Part Number:	DNF14-250M-C
RoHS Compliancy Status:	Compliant
Part Description:	Male Disconnect, nylon barrel insulated, funnel entry, 16 – 14 AWG, .250 x .032 tab.
Product Type:	Disconnects
CSA Certified:	Yes
Length (In.):	.90
Max. Ins.:	.162
Panduit Color Code:	Blue
Tab Size (In.):	.250 x .032
Tool:	CT-1550, CT-1551, CT-2500
Wire Range:	16 – 14 AWG
Min. Order UOM:	PC
Min. Order Qty.:	100
BOM Qty. (# of Pkgs.)	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

View Content Details

Add to My Catalog

Evaluate Design a Solution Part Drawings: Male Disconnect, Nylon Barrel Insulate...

Design a Solution

Part Drawings:



Male Disconnect, Nylon Barrel Insulated - Funnel Entry pdf

PANDUIT PART			रा ।		MAV	DIV		C :										
	NUMBER		WIRE	MAX. WIRE	DIMENSIONS			HOUS	NG									
	PRE	EFIX		PKG	RANGE AWG	INSUL. DIA.	A *.03	В *.01	C ±.002	COL								
D	NF18	-250	M	- C - M	22-18	.136 (3,5)	.90 (22,9)	.25 (6,4)	.032 (0,81)	RED	ı							
D	NF 14	-250	M	- C - M	16-14	.162 (4,1)	.90 (22,9)	.25 (6,4)	.032 (0,81)	BLUI	Ξ							
DN	NF10-	2501	/ 1*	-L -D	12-10	.230 (5,8)	1.03 (26,2)	.25 (6,4)	.032 (0,81)	YELL	OW						WIRE-	
*NOT UL LISTED OR CSA CERTIFIED SERRATED BARREL - INSUL. DIA.																		
NOTES:																		
1. CSA CERTIFIED FOR: A. 600V. MAX. VOLTAGE RATING B. 221° F (105° C) MAX. TEMP. RATING C. FOR STRANDED COPPER WIRE ONLY WIRE ENTRY																		
2. MATERIAL: A. STAMPING032 (.81) THK COPPER,NICKEL PLATED B. HOUSING - NYLON C. SLEEVE - BRASS, TIN PLATED)		H		ING —		SLEEVE			
3. PACKAGE QTY: STD. PKGL=50																		
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS																		
	5. INSTALLATION TOOLS: A. CSA CERTIFIED: CT-100, CT-1550, CT-1551 B. PANDUIT APPROVED: CT-160, CT-260																	
6. WIRE STRIP LENGTH: 9/32 +1/32 -0 (7.1 +0.8 -0)																		
08	11/04	KLFU			ADDED LO	OGO AND N	MARK I NO	5 10]			RTIFIED R31212		A41322_	.08
07	7/01	JAMBR	LS	ADDE	D PACKAG	ING COLL	IMN TO	TABLE	0949	98 TRO	JAC			157				
06	1/01	RM S	кв			/AS N413			0892	25 TRO	JCJ			، اا	CORP.	TINLEY	PARK, ILLINO	DIS
05	10/00	SB S	SKB	ADDEI CT-5	D DNF10-2 50 TOOLS	50M AND R	EMOVED	CT-500 8	0873	9 TRO) JCJ	NY			ATED MAI LED WIR			СТ
04	3/99	JD S	KB	ADDE	O CT-1551	& CT-155	0 TOOLS		0763	34 TRO) JCJ	. 250) X .03	32 (6.35 X	0.81) MALE	TAB
REV	DATE	BY C	CHK		D	ESCRIPTION			ECN #	PM	CUST	DAWN BY	RL	S	NONE	DRAWING N	. A4132	22