## World Leader in Network and Electrical Solutions

Printer Friendly

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

**SEARCH** 

Current refinements (click 

to remove)

Search Tips 👩

miliai, Non-insulated 🔼 Text Search. F14-14K-C

Your search criteria matched only one product, shown below.

- Ring tongue design assures a secure connection in high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Brazed seam protects terminal barrel from splitting during the crimp process
- Barrel of terminal internally beveled to provide quick and easy wire insertion
- UL and CSA rated up to 2000 V per UL 486
- Maximum recommended operating temperature 302°F (150°C)

‡UL and CSA approved tooling/product combinations.

Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.



Add to My Catalog

Part Number:	P14-14R-C
RoHS Compliancy Status:	Compliant
Part Description:	Ring Terminal, 18 – 14 AWG, 1/4" stud size, non-insulated.
Product Type:	Terminals
CSA Certified:	Yes
UL Listed:	Yes
Length (In.):	.91
Width (In.):	.46
Angle:	straight
Clearance:	.38
Stock:	.03
Stud Size:	1/4"
Tool:	CT-100A‡, CT-200‡, CT-600-A‡, CT-1570‡, CT-2500‡
Wire Range:	18 – 14 AWG
Wire Range (mm²):	1.0 - 2.5
Min. Order UOM:	PC
Min. Order Qty.:	100
BOM Qty. (# of Pkgs.)	


Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

PANDUIT PART NUMBER		STUD SIZE	DIMENSIONS in.					
			A ±.03	W ±.01	C MIN	M ±.03	H ±.01	
P14-4R	- C - M	#4	.62 (15.8)	.25 (6.4)	.20 (5.1)	.50 (12.7)	.12 (3.1)	
P14-6R	- M	#6	.62 (15.8)	.25 (6.4)	.20 (5.1)	.50 (12.7)	.15 (3.8)	
P14-8R	- C - M	#8	.71 (18.0)	.31 (7.9)	.25 (6.4)	.55 (14.0)	.17 (4.3)	
P14-10R	- C - M	#10	.71 (18.0)	.31 (7.9)	.25 (6.4)	.55 (14.0)	.20 (5.1)	
P14-14R	- C - M	1/4"	.91 (23.1)	.46 (11.7)	.38 (9.7)	.68 (17.3)	.27 (6.9)	
P14-56R	-С -М	5/16"	.91 (23.1)	.46 (11.7)	.38 (9.7)	.68 (17.3)	.34 (8.6)	
P14-38R	- C - M	3/8"	1.00 (25.4)	.53 (13.5)	.43 (10.9)	.73 (18.5)	.40 (10.2)	
P14-12R	-L	1/2"	1.20 (30.5)	.72 (18.3)	.53 (13.5)	.84 (21.3)	.52 (13.2)	

## NOTES:

- 1. UL LISTED AND CSA CERTIFIED FOR: A. 18-14 AWG SOLID OR STRANDED COPPER WIRE
- 2. MAXIMUM RECOMMENDED OPERATING TEMP. NOT TO FXCFFD 150° (302°F)
- MATERIAL: A. STAMPING - .03" (.8) THK COPPER, TIN PLATED
- -L=50STD. PKG. -C=100 PACKAGE QTY: BULK PKG. -M=1000
- 5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- 6. INSTALLATION TOOLS:
  - UL LISTED AND CSA CERTIFIED: CT-100,CT-200, CT-570, CT-1570 PANDUIT APPROVED: CT-160, CT-260
- 7. WIRE STRIP LENGTH: 9/32 +1/32 (7.1 +.8 )







A41264\_06

	•	•	•••	





TRO

06 12/03 KLFU REMOVED NOTE 1B, ADDED NOTE 2 TINLEY PARK, ILLINOIS 05 5/02 SRBSKB 10231 CHANGED (DIMS) TO 1 PL DECIMAL LA

10171

ECN #

#16-14 BARREL NON-INSULATED RING TONGUE

04 4/02 SRB - -

DATE BY

ADDED P14-12R CHK

DESCRIPTION

CUST

DAW

RLS

NONE

A41264