	۵	support locate distributor about panduit	t careers worldwide
	DUIT World Leader in Network	and Electrical Solutions	Printer Friendly
	RESOURCES PRODUCTS SERVICES LEARNING	SEARCH	
	s (click 🛛 to remove)		Search Tips 🍘
🔀 Region 🕨 USA 🔀 F	Product Family F Ring Terminal, Non-Insulated – High Tempera	—	
	Your search criteria matched only one	Product, shown below.	
	 Brazed seam protects terminal barre 	od wire contact and maximum tensile strength el from splitting during the crimp process to provide quick and easy wire insertion	
Part Number:	P18-6RHT6-C		
RoHS Compliancy Status:	Compliant		
Part Description:	High Temperature Ring Terminal, 22 – 18 AWG, #6 stud size,	non-insulated.	
Product Type:	Terminals		
Length (In.):	.62		
Width (In.):	.25		
Angle:	straight		
Clearance:	.21		
Stock:	.03		
Stud Size:	#6		
Tool:	CT-100A, CT-200, CT-600-A, CT-1570, CT-2500		
Wire Range:	22 – 16 AWG		
Wire Range (mm ²):	0.5 - 1.5		
Min. Order UOM:	PC		
Min. Order Qty.:	100		
BOM Qty. (# of Pkgs.)			
Add to My Catalog			

Add to My Catalog


Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

ſ	PANDU I T	STUD S1ZE	DIMENSIONS in.							
	PART NUMBER		A *•03	W *•010	C MIN.	M *•03	H *•010			
	P18-6RHT6	#6	.62 (15.75)	25 (6.35)	_21 (5,33)	.50 (12.70)	_15 (3_81)			
	P18-8RHT6	#8	.71 (18.03)	.31 (7.87)	25 (6.35)	.55 (13.97)	_17 (4_32)			
	P18-10RHT6	#10	.71 (18.03)	.31 (7.87)	_25 (6_35)	.55 (13.97)	20 (5.08)			



- 1. RECOMMENDED FOR: A. #22-16 AWG SOLID OR STRANDED COPPER WIRE B. 650° F (343° C) MAX. TEMP. RATING
- 2. MATERIAL: A. STAMPING- .03" (.76) THK COPPER, NICKEL PLATED
- 3. PACKAGE QTY: STD. PKG. -C=100 BULK PKG. -M=1000
- 4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- 5. INSTALLATION TOOLS: A. PANDUIT APPROVED: CT-100, CT-200, CT-160, CT-260, CT-570, CT-1570
- 6. WIRE STRIP LENGTH: 9/32 *1/32.0 (7.1***.0)



A41265_04

04	1/01	RM		FILESPEC WAS N41265AA_PCD_03								
0Э		JKD		ADDED CT-1570 TOOL	07632			│ ■ZA	NDULT	CORP.	TINLEY PARK, ILLINOIS	
2	3-95	MS	RLS	UPDATED NOTES AND DIMENSIONS	03037	LCA	ĸs	#22-18 BARREL NON-INSULATED RING				
1	7-88	D₩		REDRAWN WITH REVISIONS		JB		TONGUE, HIGH TEMPERATURE, 650° F				
REV	DATE	BY	СНК	DESCRIPTION	ECN .	CUST	РМ		CHAID RLS	NONE	A41265	