World Leader in Network and Electrical Solutions

Printer Friendly

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

SEARCH

Current refinements (click x to remove)


Search Tips 6

🗵 Region 🕽 USA 🔀 Product Family 🕽 Locking Fork Terminal, Vinyl Insulated – Funnel Entry 🔀 Text Search: 'PV14-6LF-C'

Your search criteria matched only one product, shown below.

- Locks in place for secure connection
- Fork design provides for fast and easy installation, without the need to remove fastener
- Insulation support helps to prevent wire damage in bending applications
- UL Flammability UL 94V-0, maximum insulation temperature 221°F (105°C)
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL and CSA rated to 600 V per UL 486

‡UL and CSA approved tooling/product combinations.



BOM Qty. (# of Pkgs.)

PC

100

Add to My Catalog

Min. Order UOM:

Min. Order Qty.:

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT	STUD SIZE	DIMENSIONS in.					
PART NUMBER		A *.03	W *=01	C *.02	W **03	H *•01	
PV14-6LF	#6	.90 (22.86)	.25 (6.35)	.22 (5.59)	.68 (17.27)	.14 (3.56)	
PV14-6LFW	#6	.90 (22.86)	.29 (7.37)	.22 (5.59)	.68 (17.27)	.14 (3.56)	
PV14-8LF	#8	.97 (24.64)	.29 (7.37)	_25 (6.35)	.73 (18.54)	_16 (4_06)	
PV14-10LF	#10	.97 (24.64)	.33 (8.38)	_25 (6.35)	.73 (18.54)	.19 (4.83)	
PV14-10LFN	#10	.97 (24.64)	.29 (7.37)	.25 (6.35)	.73 (18.54)	.19 (4.83)	

NOTES:

- I. UL LISTED & CSA CERTIFIED FOR
 - A. 600 V. MAX. VOLTAGE RATING (1000 V. MAX. IN SIGNS, FIXTURES AND LUMINAIRES.)
 - B. 18-14 AWG SOLID OR STRANDED COPPER WIRE & 221°F (105°C) MAX TEMP RATING. WITH THE CT-500 & CT-550, CT-1550, CT-1551 INSTALLATION TOOLS.
 - C. 16-14 AWG SOLID OR STRANDED COPPER WIRE & 167°F (75°C) MAX TEMP RATING WITH THE CT-100 INSTALLATION TOOLS.
- 2. MATERIAL:
 - A. STAMPING .032 (.81) THK COPPER, TIN PLATED B. HOUSING - VINYL. BLUE
- 3. STRIP LENGTH 5/16 *1/32.0
- 4. PACKAGE QTY.: -C=100/-M=1000
- 5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS



LISTED 587H E52164





A41296_09

REV	DATE	BY	СНК	DESCRIPTION	ECN •	CUST	РМ	0
6	8-88	D₩		REDRAWN WITH REVISIONS			JRB	
7	1-95	MC	RLS	UPDATED NOTES AND DIMENSIONS	02896	LCA	TFKE	
08		JKD		ADDED CT-1550 & CT-1551	07634			
09	1-01		RM	FILESPEC WAS N41296AA_PCD_08				

	ORP
--	-----

P.

TINLEY PARK, ILLINOIS

#16-14 BARREL FUNNELED VINYL INSULATED LOCKING FORK. .175 (4.45) MAX. WIRE INSULTION DIAMETER

DAW CJH 741296 NONE