## PANDUIT \*


## ABM2S-A-D



- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with PANDUIT cable ties for a complete wire routing solution
- ‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

■ Part Number	ABM2S-A-D
■ RoHS Compliancy Status	Compliant
■ Part Description	4-Way Adhesive Backed Cable Tie Mount
■ Product Type	Cable Tie Mounts - Adhesive Backed
■ Material	ABS
■ Color	White
■ UL Recognized	E136577
■ Height (In.)	.16
■ Height (mm)	4.2
■ Length (In.)	1.00
■ Length (mm)	25.4
■ Width (In.)	1.00
■ Width (mm)	25.4
■ Adhesive Type	Rubber
<ul> <li>CE Compliant</li> </ul>	CT-ACC1 / 10.96
<ul><li>Environment</li></ul>	Indoors
■ Max. Bundle Diameter (mm	) 4.8
■ Mounting Method	Adhesive Backed
■ Pricing Description	Cable Tie Mount, Adh., 1"x1" (25.4mm x 25.4mm), WH
■ Screw Size	#6 (M3)
■ Screw Size Metric	M3
<ul> <li>Used With Cable Ties</li> </ul>	M, I, S, SGM, SGI
■ Min. Order UOM	PC
<ul><li>Min. Order Qty.</li></ul>	500
■ BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NUMBER*	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT  bs/100 pcs (g)/100 pcs		
ABM2S-A	MINIATURE INTERMEDIATE STANDARD	0.23 (107)		

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

TO APPLY MOUNTS:

- 1. REMOVE MOUNT FROM THE PROTECTIVE LINER.
  2. PLACE IN DESIRED LOCATION.
  3. APPLY PRESSURE TO TOP SURFACE OF MOUNT.



## NOTES:

- \* 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2. MOUNTS PROVIDED IN STRIPS OF TWO FOR EASY REMOVAL FROM LINER.
- 3. MOUNT HAS CONTINUOUS OPERATION TEMPERATURE OF 120°F (49°C).

					DIMENSIONS IN BRACKETS ARE METRIC [ mm ]								
							G00239CF_PB_ABM2S_09						
											YDUIT corp.		
										لــــــــــــــــــــــــــــــــــــــ	UPULL CORP.	TINLEY PARK, ILLINO	IS
										ABM2S-A			
										ADHESIVE BACKED MOUNT			
											THERWISE SPECIFIED, NAL TOLERANCES ARE:	UNLESS OTHERWISE SPECIFIED,	
9	3/3/05	3		REMOVE ABM25	G80239CF	9				(.XX) ±0.05 (1.31 (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.51 ANGLES ±5*		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
8	7/9/03	Ş		CHANGED TOLERANCE ON .203 AND .067 DIMENSION FROM .010 (.25) TO .015 (.38)	980239CF	8				DRWH BY MJK	MAT'L:	SCALE NONE	
7	5/27/03	3		CORRECTED WINDOW WIDTH DIMENSION	GB0239CF	7				DATE 11/3/94	ABS	DRAMING NO.	ρ <b>ω</b> ο Δ
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP		CHK.D		GB0239CF	S12E