PANDUIT

ILT4LH-TL0




- Greater resistance to damage caused by ultraviolet light indoor or outdoor use
 - Parallel-entry cable tie that threads like a belt (180° entry)
 - Low profile head avoids snags and reduces overall bundle size
 - 35% lower head height than conventional 90° ties
 - Parallel-entry limits exposure to sharp edges and protects workers' arms/hands
 - Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

| ■ Part Number | ILT4LH-TL0 |
|---|--|
| ■ RoHS Compliancy Status | Compliant |
| ■ Part Description | Belt-Ty™ In-Line Cable Tie, 14.8", Light-Heavy cross section |
| ■ Product Type | Cable Ties |
| ■ Material | Weather Resistant Nylon 6.6 |
| - Color | Black |
| CSA Certified | No |
| ■ UL Listed (File #E56854) | No |
| ■ UL Recognized (File #E56854) | No |
| ■ Length (In.) | 14.8 |
| ■ Length (mm) | 376 |
| ■ Width (In.) | .300 |
| ■ Width (mm) | 7.6 |
| ■ CE Compliant | Yes |
| Cross Section | Light-Heavy |
| Head Height (In.) | .250 |
| ■ Head Height (mm) | 6.4 |
| ■ Head Width (In.) | .515 |
| ■ Head Width (mm) | 13.1 |
| ■ Locking Style | Locking |
| Material Flammability Rating | UL 94 HB |
| ■ Max. Bundle Diameter (In.) | 4.00 |
| ■ Max. Bundle Diameter (mm) | 102 |
| Max. Continuous Use Temperature | 185°F (85°C) |
| ■ Min. Loop Tensile Strength (Lbs.) | 120 |
| ■ Min. Loop Tensile Strength (N) | 534 |

| ■ Pricing Description | Cable Tie, In-Line, 14.8"L (376mm), Light-Heavy, Weather Resistant, Black |
|-------------------------|---|
| ■ Thickness (In.) | .075 |
| ■ Thickness (mm) | 1.9 |
| ■ Tool | GTH, GS4H, GS4EH, PTH, STH2, ST3EH |
| ■ Min. Order UOM | PC |
| ■ Min. Order Qty. | 250 |
| ■ BOM Qty. (# of Pkgs.) | |

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT PART NO. * | BUNDLI MIN. (mm) | MAX. in | A in (mm) | B in (mm) | C in (mm) | D in (mm) | E in (mm) | F in (mm) | MIN. LOOP TENSILE LBS. (N) | CROSS SECTION | TIP STYLE | WEIGHT bs/100 pcs. (g) |
|-----------------------|---------------------|-----------------|---------------|---------------|----------------|---------------|----------------|---------------|----------------------------------|------------------|--------------|-------------------------------|
| ILT2S | .188 (4.8) | 1.88 (47.8) | .052 (1.3) | .190 (4.8) | .389 (9.9) | .140 (3.6) | .316 (8.0) | 8.30 (211) | 50 (222) | STANDARD | CURVED | .284 (129) |
| ILT3S | .188 (4.8) | 3.00 (76.2) | .052 (1.3) | .190 (4.8) | .389 (9.9) | .140 (3.6) | .316 (8.0) | 11.5 (292) | 50 (222) | STANDARD | CURVED | .385 (175) |
| ILT4S | .188 (4.8) | 4.00 (101.6) | .052 (1.3) | .190 (4.8) | .389 .9.9 | .140 (3.6) | .316 (8.0) | 14.7 (373) | 50 (222) | STANDARD | CURVED | .490 (222) |
| ILT4LH | .200 (5.1) | 4.00 (101.6) | .075 (1.9) | .300 (7.6) | .600 (15.2) | .250 (6.4) | .515 (13.1) | I I | 120 (534) | LIGHT HEAVY | CURVED | 1.132 (514) |
| ILT6LH | .200 (5.1) | 6.00 (152.4) | .075 (1.9) | .300 (7.6) | .600 (15.2) | .250 (6.4) | .515 (13.1) | | 120 (534) | LIGHT HEAVY | CURVED | 1.610 (731) |

| | | | | | | | | | DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS |
|-----|---------|------|-----|---------------------------------|-------|---|------|-----|--|
| | | | | | | | | | SS_27217_ILT_04.PRT |
| | | | | | | | | | ANDUIT CORP. TINLEY PARK, ILLINOIS |
| | | | | | | | | | BELT-TY INLINE-TIE CABLE TIES |
| | | | | | | | | | ILT SERIES |
| | | | | | | | | | UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: ALL DIMENSIONS ARE GIVEN |
| | | | | | | | | | (.X) ± (.XXX) ±,020(.51) (.XX) ±.02(.5) ANGLES ± IN INCHES, THIRD ANGLE PROJECTION. |
| | | | | | | | | | DRAWN BY CJW MAT'L; SCALE NONE |
| 7 | 8/10/04 | MJVE | | .515 WAS .475 ON ILT4/6LH DIM E | 27217 | 7 | | | DATE DRAW ING NO. DWG 6-9-99 A |
| REV | DATE | вү | СНК | DESCRIPTION | ECN - | R | CUST | SUP | SS-27217 A |