




## LWC19-A-C



- Routes and secures cords and cables
- Convenient releasable latch
- Available in six sizes with releasable latch
- Rubber-based adhesive provides a strong and reliable bond

■ Part Number	LWC19-A-C
■ RoHS Compliancy Status	Compliant
■ Part Description	Adhesive Backed Latching Wire Clip
■ Product Type	Mounting Device
■ Material	Nylon 6.6
■ Color	Natural
■ Height (In.)	.39
■ Height (mm)	9.9
■ Length (In.)	.85
■ Length (mm)	21.6
■ Width (In.)	.61
■ Width (mm)	15.5
■ Adhesive Type	Rubber
■ Environment	Indoors
■ Max. Bundle Diameter (In.)	.19
■ Max. Bundle Diameter (mm)	4.8
■ Mounting Method	Rubber Adhesive
■ Pricing Description	Latching Wire Clip, Adh., .19" (4.8mm) Bundle, NAT
■ Min. Order UOM	PC
■ Min. Order Qty.	100
■ BOM Qty. (# of Pkgs.)	




PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT lbs. (g)/100pcs
LWC19-A	0.1875 (4.8)	0.29 (130)

\*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION, FOR PACKAGE SIZE.

- 2) MOUNT IS DESIGNED TO SUPPORT  
0.25 lbs [227g] MAX WEIGHT ON  
A CLEAN DRY SMOOTH SURFACE.

TO APPLY LATCHING WIRE CLIP:

1. REMOVE PROTECTIVE LINER
2. PLACE IN DESIRED LOCATION
3. APPLY PRESSURE TO TOP OF LATCHING WIRE CLIP



ADHESIVE BACKING: PRESSURE SENSITIVE FOAM  
0.04 [1.0] THICK WITH PROTECTIVE LINER TO  
EXTEND BEYOND EDGE FORMING A TEAR TAB.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]			
CAD FILENAME/LAYERS		G00239EH_PB_LWC19A_01	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
LWC19-A, LATCHING WIRE CLIP			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ± 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY AJV	MAT'L:	SCALE 2X	DWG A SIZE
DATE 9-20-96	NYLON 6/6	DRAWING NO. GB0239EH	
CHK'D			