BEC75-A-L





- Beveled entry allows for easy insertion of cable bundle
- Rubber-based adhesive provides a strong and reliable bond
- Acrylic-based adhesive withstands higher temperatures and outdoor environment

■ Part Number		BEC75-A-L
■ RoHS Compliancy	/ Status	Compliant
■ Part Description		Adhesive Backed Bevel Entry
■ Product Type		Mounting Device
■ Material		Nylon 6.6
■ Color		Natural
■ UL Recognized		E136577
■ Height (In.)		.89
■ Height (mm)		22.6
■ Length (In.)		1.46
■ Length (mm)		37.1
■ Width (In.)		1.49
■ Width (mm)		37.8
 Adhesive Type 		Rubber
Environment		Indoors
■ Hole Diameter (In	.)	Em Dash
■ Hole Diameter (m	m)	Em Dash
■ Max. Bundle Diam	neter (In.)	.75
■ Max. Bundle Diam	neter (mm)	19.0
■ Mounting Method		Rubber
■ Pricing Description	n	Bevel Entry Cord Clip, Adh., .7
■ Min. Order UOM		PC
■ Min. Order Qty.		50
■ BOM Qty. (# of Pk	(gs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1.49	
------	--


0.89		Pacioun	
_\$	-	— 1.46 — [37.1]	>

PANDUIT PART NO. *	WEIGHT LBS / 100 [G]/PCS.
BEC75-A	1.28 [582]
BEC75-AT	1.28 [582]

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

NOTES:

- 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- 2. TO APPLY MOUNT: 6) REMOVE PROTECTIVE LINER: 6) PLACE IN DESIRED LOCATION: c) APPLY PRESSURE TO TOP OF MOUNT.



SCALE: FULL

ADHESIVE TAPE: PRESSURE SENSITIVE FOAM 0.04 [1.0] THICK WITH RUBBER ADHESIVE AND PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 1.09 lbs. [493g] MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH, GREASEFREE SURFACE.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G00239CH_PB_BEC75_01

									CORP. TINLEY PARK, ILLINOIS
									BEC75 BEVEL ENTRY CLIP
									UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± N/A (.XXX) ± N/A (.XX) ± .020 (.5) ANGLES ± N/A UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
1	5-9-06	TMSA	UPDATED PICTORIALLY	GB0239CH	1				DRAWN BY GDH MAT'L: SCALE 1 1/2X
R	11-30-94	GDH	INITIAL RELEASE	GB0239CH	R				DATE 11-30-94 6/6 NYLON DRAWING NO.
REV	DATE	BY CHK	DESCRIPTION	ECN -	R	CUST	SUP		GB0239CH A