

PMCC38H25-C



PMCC38H25-C Part Number RoHS Compliancy Status Compliant Part Description Push Barb Mount Cord Clip Product Type Mounting Device Material Nylon 6.6 Color Natural UL Recognized E136577 Height (In.) .38 9.7 Height (mm) Length (In.) .50 Length (mm) 12.7 • Width (In.) .50 Width (mm) 12.7 Environment Indoors UL94 V-2 Flammability Rating Max. Bundle Diameter (In.) .38 • Max. Bundle Diameter (mm) 9.6 Max. Panel Thickness (In.) .105 Max. Panel Thickness (mm) 2.7 Mounting Method Push Barb Panel Hole Diameter (In.) .250 Panel Hole Diameter (mm) 6.4 Pricing Description Cord Clip, Push Mount, .38" (9.7mm) Bundle, NAT .89 • Total Height (In.) Total Height (mm) 22.9 Min. Order UOM PC

100

• Min. Order Qty.

- • Cables are easily snapped into or out of clips
 - The winged design holds mount in place even in applications where vibration is present
 - Design of wing provides added stability

