

RER.75-S6-X



• As wires are individually inserted, the bundle is pre-formed. When harness is complete it can be easily snapped out. Three sizes available for 1/2" (12.7mm) 3/4" (19.0mm) and 1 1/4" (31.7mm) bundles.

■ Part Number	RER.75-S6-X
■ RoHS Compliancy Status	RoHS directive is not applicable
■ Part Description	Harness Board Elastic Bundle Retainer
■ Product Type	Harness Board Accessories
■ Material	Nylon 6.6
- Color	Black Base, White Arm
- Height (In.)	2.21
■ Height (mm)	56.1
■ Length (In.)	1.18
■ Length (mm)	30.0
■ Width (In.)	1.12
■ Width (mm)	28.4
■ Arm Color	White
 Arm Material 	Acetal
 Base Color 	Black
 Base Material 	Nylon
■ Environment	Indoors
■ Hole Space (In.)	.83
■ Max. Bundle Diameter (In.)	.75
Max. Bundle Diameter (mm)	19.0
■ Mounting Method	Two #6 (M3) Screws
 Pricing Description 	Elastic Retainer, Rep, .75" (19.1mm) Bundle, #6 Screw (M3)
■ Screw Size	#6 (M3)
 Screw Size Metric 	M3
Min. Order UOM	PC
■ Min. Order Qty.	10

