## PANDUIT

## BT1.5I-M0



- Greater resistance to damage caused by ultraviolet light indoor or outdoor use
  - Dome-top head features unique patented design with round, smooth edges
  - Stainless steel locking barb provides consistent performance, reliability and infinite adjustability through entire bundle range
  - High strength and low thread force
  - Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Light-Heavy cross section ties have a straight tip)

■ Part Number	BT1.5I-M0
■ RoHS Compliancy Status	Compliant
■ Part Description	Cable Tie with metal barb, 6.1", Intermediate cross section
■ Product Type	Cable Ties
■ Material	Weather Resistant Nylon 6.6
- Color	Black
<ul> <li>CSA Certified</li> </ul>	Yes
■ UL Listed (File #E56854)	Yes
■ UL Recognized (File #E56854)	Yes
■ Length (In.)	6.1
■ Length (mm)	155
■ Width (In.)	.141
■ Width (mm)	3.6
■ CE Compliant	Yes
<ul> <li>Cross Section</li> </ul>	Intermediate
<ul><li>Head Height (In.)</li></ul>	.185
■ Head Height (mm)	4.7
■ Head Width (In.)	.248
■ Head Width (mm)	6.3
■ Locking Style	Locking
■ Material Flammability Rating	UL 94V-2
■ Max. Bundle Diameter (In.)	1.50
■ Max. Bundle Diameter (mm)	38
<ul> <li>Max. Continuous Use Temperature</li> </ul>	185°F (85°C)
■ Min. Loop Tensile Strength (Lbs.)	40
■ Min. Loop Tensile Strength (N)	178

■ Pricing Description	Cable Tie, Metal Barb, 6.1"L (155mm), Intermediate, Weather Resistant, Black
■ Thickness (In.)	.041
■ Thickness (mm)	1.0
■ Tool	GTS, GTSL, GS2B, PTS, PPTS, STS2
■ Min. Order UOM	PC
■ Min. Order Qty.	1000
■ BOM Qty. (# of Pkgs.)	

