BT2I-M0





- Greater resistance to damage caused by ultraviolet light indoor or outdoor use
 - Dome-top head features unique patented design with round, smooth edges
 - Stainless steel locking barb provides consistent performance, reliability and infinite adjustability through entire bundle range
 - High strength and low thread force
 - Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Light-Heavy cross section ties have a straight tip)

■ Part Number	BT2I-M0
■ RoHS Compliancy Status	Compliant
■ Part Description	Cable Tie with metal barb, 8.0", Intermediate cross section
■ Product Type	Cable Ties
■ Material	Weather Resistant Nylon 6.6
- Color	Black
 CSA Certified 	Yes
■ UL Listed (File #E56854)	Yes
■ UL Recognized (File #E56854)	Yes
■ Length (In.)	8.0
■ Length (mm)	203
■ Width (In.)	.141
■ Width (mm)	3.6
■ CE Compliant	Yes
Cross Section	Intermediate
Head Height (In.)	.185
■ Head Height (mm)	4.7
■ Head Width (In.)	.248
■ Head Width (mm)	6.3
■ Locking Style	Locking
■ Material Flammability Rating	UL 94V-2
■ Max. Bundle Diameter (In.)	2.00
■ Max. Bundle Diameter (mm)	51
 Max. Continuous Use Temperature 	e 185°F (85°C)
■ Min. Loop Tensile Strength (Lbs.)	40
■ Min. Loop Tensile Strength (N)	178

■ Pricing Description	Cable Tie, Metal Barb, 8.0"L (203mm), Intermediate, Weather Resistant, Black
■ Thickness (In.)	.041
■ Thickness (mm)	1.0
■ Tool	GTS, GTSL, GS2B, PTS, PPTS, STS2
■ Min. Order UOM	PC
■ Min. Order Qty.	1000
■ BOM Qty. (# of Pkgs.)	

