## World Leader in Network and Electrical Solutions

**Printer Friendly** 

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING


SEARCH

Current refinements (click **x** to remove)

Search Tips 7

🗵 Region 🕽 USA 🔀 Product Family 🕽 Female Disconnect, Nylon Barrel Insulated – Funnel Entry 🔀 Text Search: 'DNF18-110-C'


Your search criteria matched only one product, shown below.



- · Barrel insulated design provides protection from electrical shorts
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection
- UL Flammability UL 94V-2/HB, maximum insulation temperature 194° F (90°C)

**Related Products** 

Male Disconnect, Nylon Barrel Insul.. **Pneumatic Crimping Tool** Contour Crimp™ Control... Wire and Cable Stripping Tools



Height (In.): .08 Length (In.): .69 Width (In.): .15 Max. Ins.: .100 Panduit Color Code: Red Tab Size (In.): .110 x .032 CT-600-A‡, CT-1525‡, CT-2500‡ Tool: Wire Range: 22 - 18 AWG Min. Order UOM: PC


Min. Order Qty.: 100

BOM Qty. (# of Pkgs.)

Add to My Catalog

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

PART NUMBER	TAB SIZE	WIRE RANGE awg	MAX. INSUL. DIA.	DIMENSIONS in.		
PART NUMBER	IND SIZE			A ±.03	В ±.01	C *.01
DNF18-110	.110 X .032	22-18	.100	.69	.15	.08
	(2.8 X 0.8)	(0,5-1,0)	(2.54)	(17.5)	(3.8)	(2.0)
DNF18-111	.110 X .020	22-18	.100	.69	.15	.07
	(2.8 X 0.5)	(0,5-1,0)	(2.54)	(17.5)	(3.8)	(1.8)



## NOTES:


REV DATE BY CHK

- 1.UL LISTED AND CSA CERTIFIED FOR:
  - A. 300V. MAX. VOLTAGE RATING
  - B. #22-18 AWG STRANDED COPPER WIRE ONLY
  - 194° F (90° C) MAX. TEMP. RATING
- MATERIAL: 2.
  - STAMPING .010" (0.25) THK BRASS,
  - TIN PLATED SLEEVE - BRASS, TIN PLATED
  - HOUSING- NYLON, RED
- PACKAGE QTY: STD. PKG. -C= 100 BULK PKG. -M= 1000
- INITIAL INSERTION FORCE 12 LB. (53 N) MAX INITIAL WITHDRAWAL FORCE - 12 LB. (53 N) MAX 6 LB. (27 N) MIN
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS OR mm2
- INSTALLATION TOOLS: A. UL LISTED & CSA CERTIFIED: CT-520, CT-1525 B. PANDUIT RECOMMENDED: CT-100
- 7. WIRE STRIP LENGTH:  $9/32^{+1/32}$  (7.1 +.8 -0)



ECN #





A41308\_05

TINLEY PARK, ILLINOIS

05	7/03	KLFU		UPDATED DRAWING				Ī
04	5/98	ТМ	WL	ADDED CT-1525 TO TOOL NOTES	06872	LA	DH	
03	6/95	MS	RS	UPDATED NOTES AND DIMENSIONS	03370	LA	KS	Ī
02	11/94	ТН	RS	UPDATED NOTES AND DIMENSIONS	02689	LA	TK	
								г

DESCRIPTION

#22-18 BARREL NYLON INSULATED FEMALE DISCONNECT. FUNNELED WIRE ENTRY

NONE A41308 DAW CUST PM