## World Leader in Network and Electrical Solutions

Printer Friendly

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

**SEARCH** 


Current refinements (click **x** to remove)

Search Tips 🕜

☑ Region > USA ☑ Product Family > Female Disconnect, Nylon Fully Insulated – Funnel Entry ☑ Text Search: 'DNF18-110FIB-C'

Your search criteria matched only one product, shown below.

DiscoGrip™ Male Discon...



- Premium nylon insulation retains its shape when crimped and provides a tight grip around the wire insulation for maximum strain relief
- Fully insulated design provides protection from electrical shorts
- Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection
- Disconnects available in common industry tab sizes
- UL and CSA rated up to 600 V per UL 310




Part Number:	DNF18-110FIB-C
RoHS Compliancy Status:	Compliant
Part Description:	Female disconnect, nylon fully insulated, funnel entry, 22 – 18 AWG, .110 X .032 tab size.
Product Type:	Disconnects
CSA Certified:	Yes
UL Listed:	Yes
Height (In.):	.16
Length (In.):	.71
Width (In.):	.19
Max. Ins.:	.120
Panduit Color Code:	Red
Tab Size (In.):	.110 x .032
Tool:	CT-100A, CT-600-A, CT-1525‡, CT-2500‡
Wire Range:	22 – 18 AWG
Min. Order UOM:	PC
Min. Order Qty.:	100
BOM Qty. (# of Pkgs.)	
Add to My Catalan	

Add to My Catalog

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



## NOTES:

- 1. UL LISTED AND CSA CERTIFIED FOR:
  A. 600V MAX VOLTAGE RATING
  - B. 257°F (125°C) MAX TEMP RATING (UL)
    221°F (105°C) MAX TEMP RATING (CSA)
  - C. STRANDED COPPER WIRE ONLY
- 2. 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
- 3. PACKAGE QTY: -M=1000 PIECES, -C=100 PIECES
- 4. MATERIAL:
  A. STAMPING: TIN PLATED BRASS
  B. HOUSING: TYPE 6/6 NYLON
- 5. DIMENSIONS IN BRACKETS ARE IN mm OR mm2
- 6. NYLON HOUSING IS TRANSLUCENT
- 7. INSTALLATION TOOLS:
  A. UL & CSA APPROVED: CT-520, CT-1525
  (UTILIZE CT-1525 CRIMP POCKET "A")
  B. PANDUIT APPROVED: CT-100
- 8. WIRE STRIP LENGTH 9/32 +1/32 (7.1 +.8 -0)

PART NUMBER		TAB SIZE	KANGE	HOUSING COLOR	MAX. INSUL.	DIMENSIONS in.		
PREF I X	PK	IND SIZE	AWG (MM²)	(NOTE 6)		A ±.03	B ±.015	C (.4)
DNF18-110FIB	- C - M	.110 X .032 (2,8 X 0,8)	22-18 (0,38-1,0)	RED	.12 (3,0)	.71 (18,0)	.19	.16 (4,1)
DNF18-111FIB	- C - M	.110 X .020 (2,8 X 0,5)	22-18 (0,38-1,0)	RED	.12 (3,0)	.71 (18,0)	.19 (4,8)	.16 (4,1)



INSUL. DIA. (SEE CHART)



A41544\_04

04	2/07	DAW	DAW	ADDED POCKET "A" NOTE TO CT-1525	TR00220	LCA	TRO			
03	7/03	KLFU	SKB	UPDATED DRAWING	12453	SKB	TRO	CORP. TINLEY PARK, ILLINOIS		
02	5/98	ТМ	JW	ADDED CT-1525 TO TOOL NOTES	06872	LA	DBH	LOOSE PIECE, NYLON, FULLY INSULATED		
01	10/94	I	RLS	UPDATED NOTES AND DIMENSIONS	02550	LA	KS	FEMALE DISCONNECTS .110 X .032, .110 X .020 TAB SIZES		
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	РМ	BDK CHK'D SCALE NONE DRAWING NO./CAD FILENAME 41544A		