

MPMWH32-L0



• Used to secure wire cable or tubing to masonry surfaces. Installed quickly into pre-drilled holes. Design holds bundle securely.

Part Number	MPMWH32-L0
 RoHS Compliancy Status 	Compliant
■ Part Description	Masonry Push Barb Cable Tie Mount
Product Type	Cable Tie Mounts - Push Mount
Material	Impact Modified Weather Resistant Nylon 6.6
■ Color	Black
Height (In.)	.28
Height (mm)	7.1
■ Length (mm)	35.8
■ Width (In.)	.58
Width (mm)	14.7
■ CE Compliant	CT-ACC4 / 10.96
Environment	Outdoors
■ Grip Length (In.)	1.41
Grip Length (mm)	35.8
Hole Diameter (In.)	.32
Hole Diameter (mm)	8.0
Max. Bundle Diameter (mm)	8.4
 Mounting Method 	Tree Barb
 Pricing Description 	Masonry Push Mount, Standard, .31" (7.9mm) Hole, BL
Thickness (In.)	.57
Thickness (mm)	14.5
Used With Cable Ties	M, I, S, HS, LH, H, HLM
Min. Order UOM	PC
Min. Order Qty.	50
■ BOM Qty. (# of Pkgs.)	

