## PLT3S-C86





- Metal impregnated material allows identification by metal detectors or x-ray inspection to meet food, beverage and pharmaceutical safety standards by helping to reduce product contamination
   One-piece design with locking wedge provides low thread force and reliable installation to improve productivity and reduce operator fatigue
  - Smooth, round edges prevent cable damage and are safe and easy for installer to use
  - Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation
- For indoor use

<ul> <li>Part Number</li> </ul>	PLT3S-C86
<ul> <li>RoHS Compliancy Status</li> </ul>	Compliant
<ul> <li>Part Description</li> </ul>	Cable Tie, 11.5", Metal Detectable, Standard cross section
<ul> <li>Product Type</li> </ul>	Cable Ties
<ul> <li>Material</li> </ul>	Metal Impregnated Nylon 6.6
■ Color	Blue
<ul> <li>CSA Certified</li> </ul>	No
<ul> <li>UL Listed (File #E56854)</li> </ul>	No
<ul> <li>UL Recognized (File #E56854)</li> </ul>	No
<ul> <li>Length (In.)</li> </ul>	11.5
<ul> <li>Length (mm)</li> </ul>	291
<ul> <li>Width (In.)</li> </ul>	.190
<ul> <li>Width (mm)</li> </ul>	4.8
<ul> <li>CE Compliant</li> </ul>	No
<ul> <li>Cross Section</li> </ul>	Standard
<ul> <li>Head Height (In.)</li> </ul>	.240
<ul> <li>Head Height (mm)</li> </ul>	6.1
<ul> <li>Head Width (In.)</li> </ul>	.320
<ul> <li>Head Width (mm)</li> </ul>	8.1
<ul> <li>Locking Style</li> </ul>	Locking
<ul> <li>Material Flammability Rating</li> </ul>	UL 94-HB
<ul> <li>Max. Bundle Diameter (In.)</li> </ul>	3.00
<ul> <li>Max. Bundle Diameter (mm)</li> </ul>	76
<ul> <li>Max. Continuous Use Temperature</li> </ul>	185°F (85°C)
<ul> <li>Min. Loop Tensile Strength (Lbs.)</li> </ul>	50
<ul> <li>Min. Loop Tensile Strength (N)</li> </ul>	222
<ul> <li>Pricing Description</li> </ul>	Cable Tie, 11.5"L (291mm) Standard, Metal Detectable, Blue

<ul> <li>Thickness (In.)</li> </ul>	.057
<ul> <li>Thickness (mm)</li> </ul>	1.4
<ul> <li>Tool</li> </ul>	GTS, GTSL, GS2B, GTH, GS4H, STS2, STH2
<ul> <li>Min. Order UOM</li> </ul>	PC
<ul> <li>Min. Order Qty.</li> </ul>	100

BOM Qty. (# of Pkgs.)

