



[Back to Result](#)

BSV14X-L [Add to BOM](#) | [Add to Favorites](#)

Butt Splice, 16 – 14 AWG, vinyl insulated.

BSV14X-L replaces BSV14X-C



Product Details	Related Documents
Std. Pkg. Qty.	50
Std. Ctn. Weight (lb)	1.7000
Std. Ctn. Volume (cf)	0.0641
Std. Pallet Weight (lb)	0.0000
Std. Pallet Volume (cf)	0.000000
RoHS Compliance Status	Compliant
Note	BSV14X-L replaces BSV14X-C
Part Description	Butt Splice, 16 – 14 AWG, vinyl insulated.
Product Type	Butt Splice
UL Listed	Yes
CSA Certified	Yes
Length (mm)	26.4
Length (In.)	1.04
CE Compliant	No
Part Features	Expanded Wire Entry, Brazed Seam protects terminal barrel from splitting during crimping process, Inte
Panduit Color Code	Blue

Wire Range (mm ²)	1.5 - 2.5
Wire Range	16 - 14 AWG
Max. Ins.	0.211
Pricing Description	Butt Splice, vinyl insulated, 16 - 14 AWG.
Tool	CT-100A, CT-600-A, CT-1550, CT-1551, CT-2500
Plating Type	Tinned
Max. Ins. (mm)	5.4
Insulation	Vinyl
BMEcat - Voltage row	600 V
Min. Order Qty.	50.0000