



NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
 - A. 600V MAX VOLTAGE RATING
 - B. 221°F (105°C) MAX TEMP RATING
 - C. STRANDED COPPER WIRE ONLY
 - D. 6-12 LBS INSERTION/WITHDRAWAL FORCE
2. MATERIAL:
 - A. STAMPING-CDA 260 BRASS, TIN PLATED
 - B. HOUSING-TYPE 66 NYLON
3. DIMENSIONS IN BRACKETS ARE IN mm OR mm²
4. COLORS ARE TRANSLUCENT
5. INSTALLATION TOOLS: CT-300-1
6. PACKAGE QTY:
 - A. STD: C=100
 - B. BULK: M=1000
7. WIRE STRIP LENGTH 11/32 ^{+1/32}₋₀ (8.7 ^{+0.8}₋₀)


LISTED
20H3
E78522


CERTIFIED
LR31212

PART NUMBER	TAB SIZE	WIRE RANGE AWG	COLOR	MAX. INSUL.	DIMENSIONS in.		
					A ±.02	B ±.01	C ±.02
DNFR18-250F1B	.250 X .032	22-18 (0.5-1.0)	RED	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR18-205F1B	.205/.187 X .032	22-18 (0.5-1.0)	RED	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR18-206F1B	.205/.187 X .020	22-18 (0.5-1.0)	RED	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR14-250F1B	.250 X .032	16-14 (1.5-2.5)	BLUE	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR14-205F1B	.205/.187 X .032	16-14 (1.5-2.5)	BLUE	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)
DNFR14-206F1B	.205/.187 X .020	16-14 (1.5-2.5)	BLUE	.178 (4.52)	.60 (15.24)	.37 (9.40)	.58 (14.73)

A41197_04

04	7/03	KLFU		ADD SLOT FOR 205/206			
03	1/01	KMDS	SRB	CAD FILE SPEC. WAS N41197AA_PCD_02	8938	JAC	CCH
02	3/99	JKD		11/32 WIRE STRIP LENGTH WAS 9/32	07469		
01	1-95	MC	RLS	UPDATED NOTES AND DIMENSIONS	02895	LCA	DBH
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM



CORP. TINLEY PARK, ILLINOIS

RIGHT ANGLE
FULLY INSULATED FEMALE DISCONNECTS
.250 X .032, .205/.187 X .032/.020

DRAWN BY	CHK'D	SCALE	DRAWING NO.
DSM	RLS	NONE	A41197