

**Products**

- Products Overview
- Product Search**
- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDF-PIGGYBACK DI ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips 

Part Number > DV14-250P-M

Your search criteria matched only one product, shown below

**DV14-250P-M**



- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
- Combination of female disconnect and male tab allows versatility in points of connection
- Multiple connection points allow additional circuits to be added to existing equipment without expensive rework
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- UL Flammability UL 94V-2/HB, maximum insulation temperature 194°F (90°C)
- Rated up to 300 V

▪ Part Number	DV14-250P-M
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Piggyback Disconnect, vinyl barrel insulated, 16 – 14 AWG, .250 x .032 tab size.
▪ Product Type	Male and Female
▪ CSA Certified	No
▪ UL Listed	No
▪ Length (In.)	0.88
▪ Length (mm)	22.4
▪ Width (In.)	0.29
▪ Width (mm)	7.4
▪ CE Compliant	No
▪ Insulation	vinyl
▪ Max. Ins.	0.160
▪ Max. Ins. (mm)	4.1
▪ Panduit Color Code	Blue
▪ Plating Type	Tinned
▪ Pricing Description	Piggyback Disconnect, vinyl barrel insulated, 16 - 14 AWG, .250 x 0.032 tab size
▪ Tab Size (In.)	0.250 x 0.032
▪ Tab Size (mm)	6.3 x 0.8
▪ Temperature Rating	194 degrees Fahrenheit (90 degrees Celsius)
▪ Tool	CT-100A, CT-260, CT-1550, CT-1551, CT-2500
▪ Wire Range	16 – 14 AWG
▪ Wire Range (mm²)	1.5 – 2.5
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1000
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="button" value=""/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.