


NOTES:

- 1. PARTS ARE (c UL us) LISTED.
- 2. FOR COPPER WIRE ONLY
- 3. PANDUIT PART NUMBERS WITH A "T" ARE TIN PLATED
- 4. PKG QTY: Q = 25 L = 50 C = 100 D = 500
- 5. SEE LABEL FOR SCREW TURQUE VALUES



PANDUIT		А	PPROXI					
PART NUMBER	CONDUCTOR RANGE	BOLT SIZE	W	Н	Т	ـا	INSTALLATION TOOL	
ML8-CY	14 SOL 8 STR.	3/16	0.38	0.42	0.08	0.81		
ML8T-CY	14 SOL 8 STR.	3/16	0.38	0.42	0.08	0.81	SLOT	
ML4-CY	14 SOL 4 STR.	1/4	0.54	0.55	0.09	1.11	SCREWDRIVER	
ML4T-CY	14 SOL 4 STR.	1/4	0.54	0.55	0.09	1.11		
ML1/0-LY	14 SOL 1/0 STR.	5/16	0.73	0.79	0.09	1.57		
ML1/0T-LY	14 SOL 1/0 STR.	5/16	0.73	0.79	0.09	1.57	1/4"	
ML250-QY	6 STR 250kcmil	3/8	0.94	1.06	0.12	1.94	HEX WRENCH	
ML250T-QY	6 STR 250kcmil	3/8	0.94	1.06	0.12	1.94		

05	11/11	JHNU	RGB	REVISED ML1/0, ML1/0T WIRE RANGE: 14-1/0 WAS 8-1/0	N41569BB-C41569	RGB	RGB				
04	04/09	JESH	JESH	UPDATED NOTE WIRE RANGE 8 SOL - 1/0 STR WAS 14 SOL -1/0	STR			CORP. TINLEY PARK, ILLIN	NOIS		
03	03/09	JESH	JESH	UPDATED NOTE 1 PARTS ARE (c UL us) LISTED. WAS UL LISTED & CSA CERTIDIED				ML SERIES COPPER MECHANICAL LUGS			
				ADD NOTE 5. SEE LABEL FOR SCREW TORQU	E VAULES			CUSTOMER DRAWING			
02	03/09	JESH	JESH	UPDATED STAMP INFORMATION, AND APPROXIMATE	DIMENSIONS			DIVIDIONAL TOLLIVANOLS AND.	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN		
				REMOVED ML500-3Y FROM DRAWING REMOVED ROHS NOTE; REMOVED MADE IN U.S.A. NOTE				(A) + (AAA) +	INCHES, THIRD ANGLE PROJECTION		
01	8/07	JHNU	JHNU	CONVERTED DRAWING TO SOLIDWORKS				DRAWN BY MAT'L: SCALE NONE			
00	7/06	JHNU	LEM	DRAWING RELEASED - ROHS COMPLIANT	PC00487			DATE COPPER DRAWING NO / CAD FILE	DWG B		
REV	DATE	BY	СНК	DESCRIPTION	ECN	-R	SUP	С41569_05	SIZE		