Turnlok® Locking Devices Connectors IP20 Suitability

Pass & Seymour

legrand

Features

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Chemical-and impact-resistant nylon housing features horizontal, easygrip ribs on back body.
- Clear thermoplastic terminal chamber for clear view of terminals and wire connections.
- Exclusive, rugged integral cord grip accepts a wide range of cord widths, no external parts to snag or break off.
- NEMA configurations always visible for fast I.D. without disconnecting.
- Industrial-strength, connector contacts resist heat rise, provide excellent conductivity.
- Recessed cord-grip screw reduces screwdriver slippage, improves safety. Compatible with wire mesh strain reliefs.
- Exclusive external neoprene dust cover on 20 and 30A devices seals cable entry; optional weatherproof boots seal connection. (Sold separately, Cat.# DC-1.)
- Interior components constructed of high-grade brass material for physical and electrical integrity.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Chemical-and impact-resistant nylon housing features horizontal, easygrip ribs on back body.
- Clear thermoplastic terminal chamber for clear view of terminals and wire connections.
- Exclusive, rugged integral cord grip accepts a wide range of cord widths, no external parts to snag or break off.
- NEMA configurations always visible for fast I.D. without disconnecting.
- Industrial-strength, brass alloy plug blades resist heat rise, provide excellent conductivity.
- Recessed cord-grip screw reduces screwdriver slippage, improves safety. Compatible with wire mesh strain reliefs.
- Exclusive external neoprene dust cover on 20 and 30A devices seals cable entry; optional weatherproof boots seal connection. (Sold separately, Cat.# DC-1.)
- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability. Accepts #14 #10 AWG.
- For locking applications.
- Technical Specifications : call 1-800-223-4185 or email tech_support@pass-seymour.com for technical support.
- Technical specifications and product catalog pages are in Adobe Acrobat (PDF) format. To get the free Adobe Acrobat browser plugin, go to the



L630FI

Connectors IP20 Suitability

Catalog Number	Page (PDF)	Other Docs.	Rating A.	Rating V.	Description/Color	Cord Diameter	NEMA Config. No.	3rd Party Compliance		
<u>L530C</u>	<u>H11</u>	GW	30	125	Black Back, White Front Body	.385 - 1.150 in.	L5-30R	(UL498	FSUL WC596	G CSA
L530CBK	<u>H11</u>	GW	30	125	Black Back, Black Front Body	.385 - 1.150 in.	L5-30R	(5) UL498	FSUL WC596	G CSA
<u>L530CGCM</u> - NEW!	<u>H05</u>	GW	30	125	Connector, Black & White	.385 - 1.15 in.	L5-30R	CULus	FSUL WC596	
<u>L530FI</u>	<u>H11</u>	👩 GW	30	125	Gray Inlet		L5-30P	(5) UL498		CSA
L530FO_	<u>H11</u>	G W	30	125	Gray Outlet		L5-30R	(UL498		G CSA
<u>L530P</u>	<u>H11</u>	GW	30	125	Black Back, White Front Body	.385 - 1.150 in.	L5-30P	() UL498	FSUL WC596	G CSA
<u>L530PBK</u>	<u>H11</u>	GW	30	125	Black Back, Black Front Body	.385 - 1.150 in.	L5-30P	() UL498	FSUL WC596	G CSA
<u>L530PGCM</u> - NEW!	<u>H05</u>	GW	30	125	Plug, Black & White	.385 - 1.15 in.	L5-30P	(ULus	FSUL WC596	
<u>L530R</u>	<u>H11</u>	🧿 GW	30	125	Single Receptacle		L5-30R	(UL498	FSUL WC596	CSA

Icon Key: (1) = Instruction Sheet (2) = Representative Product Image

GW = Graphics Workshop Images

<u>All Products</u> -> <u>Residential Homeowners</u> -> <u>Turnlok® Locking Devices</u> -> <u>Locking Connectors</u> -> Connectors IP20 Suitability

Turnlok[®] Locking Devices Receptacles, Connectors, Plugs, Inlets, Outlets


3 Wire Grounding 30A, 125 & 250V, 277VAC

NEMA

3rd Party Compliance

Pass & Seymour

Dlegrand




30A Receptacle




30A Connector



30A Plug



L530, L630, L730-FI




L530, L630, L730-FO

H-11



*AC only.

Reference Pages H-31 and H-32 for Accessories.



All devices listed on this page conform to NEMA WD-1 and WD-6.

Turnlok® Locking Devices