

30 Amp NEMA L1630 Connector - Black Back, White Front Body

L1630C



Turnlok Connector 4wire 30amp 3phase
480v



features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

specifications

General Info

Color: Black, White
Type: Connector
Number Of Wires: 4

Listing Agencies/Third Party Information

CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: 498
UL Standard: Yes
UN SPS C: 39121403

Dimensions

Diameter U S: 2.20"
Length U S: 3.33"

Technical Information

Amps: 30 Amp
NEMA Configuration Number: L1630
Volts: 480V
Volts A C: 480

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant