

**M12-Round-Plug Connector, Double-Ended Cordsets, According to IEC 61076-2-101**


**RST -RKT | RST-RKWT**



**3-, 4-, and 5-Poles**


Actuator/sensor cordset, double-ended, M12, 3-, 4-, and 5-poles, male straight to female straight connector with self-locking thread and molded TPE, PUR, or PVC cable, IEC color code.

**RST-RKT**



Actuator/sensor cordset, double-ended, M12, 3-, 4-, and 5-poles, male straight to female 90° connector with self-locking thread and molded TPE, PUR, or PVC cable, IEC color code.


**RST-RKWT**



**Pin Assignments**

**M12 - Male**

**3 poles**



1 = brown  
3 = blue  
4 = black

**4 poles**



1 = brown  
2 = white  
3 = blue  
4 = black

**5 poles**



1 = brown  
2 = white  
3 = blue  
4 = black  
5 = grey



# Be Certain with Belden

## M12-Round-Plug Connector, Double-Ended Cordsets, According to IEC 61076-2-101

RST-RKT | RST-RKWT

### Technical Data

#### Environmental

Degree of protection	IP 67 / NEMA 6P
Operating temperature range	PUR: -40°C (-40°F) / +80°C (176°F) PVC: -40°C (-40°F) / +90°C (194°F) TPE: -40°C (-40°F) / +90°C (194°F)

#### Mechanical

Housing / Molded body	TPU, yellow RST 8-627: PUR, black
Insert	TPU, yellow RST 8-627: PUR, orange
Contact	CuSn, gold plated
Coupling nut	CuZn, nickel-plated
O-ring	Viton

#### Electrical

Current rating	4 A
Voltage rating	250 V 63V (713)

### Cable Specifications

Cable No.	Outer Jacket	Conductor Size	Jacket Color	OD
<b>602</b>	<b>PUR</b>	<b>18AWG</b>	Yellow	.230" (5.8 mm)
Continuous flex rating and suitable for general C-track usage. 1 million cycles at minimum bend radius 10X cable diameter.				
<b>610</b>	<b>PUR</b>	<b>22AWG</b>	Yellow	.190" (4.8 mm)
<b>612</b>	<b>PVC</b>	<b>22AWG</b>	Yellow	.210" (5.3 mm)
<b>627</b>	<b>PVC</b>	<b>24AWG</b>	Black	.232" (5.9 mm)
<b>632</b>	<b>PVC</b>	<b>22AWG</b>	Yellow	.190" (4.8 mm)
<b>633</b>	<b>PVC</b>	<b>22AWG</b>	Yellow	.190" (4.8 mm)
<b>637</b>	<b>TPE</b>	<b>18AWG</b>	Yellow	.280" (7.1 mm)
<b>643</b>	<b>TPE</b>	<b>22AWG</b>	Yellow	.246" (6.2 mm)
<b>644</b>	<b>PUR</b>	<b>22AWG</b>	Yellow	.210" (5.3 mm)
<b>645</b>	<b>PUR</b>	<b>18AWG</b>	Yellow	.220" (5.6 mm)
<b>679</b>	<b>PUR</b>	<b>22AWG</b>	Yellow	.190" (4.8 mm)
<b>713</b>	<b>TPE</b>	<b>22AWG</b>	Yellow	.280" (7.1 mm)
<b>731</b>	<b>TPE</b>	<b>18AWG</b>	Yellow	.261" (6.6 mm)

Cordsets  
Double-Ended

Part Number	Pins	Outer Jacket	Standard Cable Lengths	Characteristics
RST 3-RKT 4-3-731/...M RST 3-RKWT 4-3-731/...M	<b>3</b>	TPE	2 M / 5 M / 10 M	
RST 3-RKT 4-3-632/...M RST 3-RKWT 4-3-632/...M		PVC	2 M / 5 M / 10 M	
RST 3-RKT 4-3-645/...M RST 3-RKWT 4-3-645/...M		PUR	2 M / 5 M / 10 M	
RST 3-RKT 4-3-610/...M RST 3-RKWT 4-3-610/...M		PUR	2 M / 5 M / 10 M	
RST 4-RKT 4-637/...M RST 4-RKWT 4-637/...M	<b>4</b>	TPE	1 M / 2 M / 3 M / 5 M / 6 M / 10 M	
RST 4-RKT 4-633/...M RST 4-RKWT 4-633/...M		PVC	2 M / 5 M / 10 M	
RST 4-RKT 4-643/...M RST 4-RKWT 4-643/...M		TPE	1 M / 2 M / 5 M / 10 M	
RST 4-RKT 4-602/...M RST 4-RKWT 4-602/...M		PUR	1 M / 2 M / 3 M / 4 M / 5 M / 6 M / 10 M	
RST 4-RKT 4-679/...M RST 4-RKWT 4-679/...M		PUR	2 M / 5 M / 10 M	
RST 5-RKT 5-612/...M RST 5-RKWT 5-612/...M	<b>5</b>	PVC	2 M / 5 M / 10 M	
RST 5-RKT 5-644/...M RST 5-RKWT 5-644/...M		PUR	2 M / 5 M / 10 M	
RST 5-RKT 5-713/...M RST 5-RKWT 5-713/...M		TPE	2 M / 5 M / 10 M	
RST 8-RKT 8-627/...M RST 8-RKWT 8-627/...M	<b>8</b>	TPE	2 M / 5 M / 10 M	