

20 Amp NEMA L2120 Single Receptacle

L2120R



Turnlok Single Receptacle 5wire 20amp
3phase 120/208v



features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

specifications

General Info

Type: Single, Receptacles
Number Of Wires: 5

Listing Agencies/Third Party Information

CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: 498
UL Standard: Yes

UN SPS C: 39121403

Dimensions

Depth U S: 1.19"

Height U S: 3.28"

Width U S: 1.61"

Technical Information

Amps: 20 Amp

NEMA Configuration Number: L2120

Volts: 120/208V

Volts A C: 120/208

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant