

Datasheet Stock No: 267-3925 RS Pro SNYD Series Insulated Crimp Spade Connector, $12 \rightarrow 10$ AWG, M8 (5/16), Yellow Nylon



Product Details:

Spade


Red 0.5 - 1.5 mm² Blue 1 - 2.6 mm² Yellow 4.0 - 6.5 mm²

Approvals

UL Listed; UL Listed for Canada

Specifications:


Wire Size:	$12 \rightarrow 10 \text{ AWG}$
Stud Size:	M8 (5/16)
Width:	14mm
Insulation:	Insulated
Colour:	Yellow
Insulation Material:	Nylon
Overall Length:	30.5mm
Series:	SNYD
Contact Material:	Copper
Thickness:	1mm



Nylon Insulation

Extra Copper Sleeve

-55°C to 105°C		
High grade brass		
High grade copper		
300V		
600V		
High grade copper		



Туре	Stud	Red		Blue		Yellow	
	Size	W	L	W	L	w	L
M8	8.4					14.0	30.2
M6	6.5	12.0	27.0	12.0	27.0	12.0	31.5
M5	5.3	9.5	20.9	9.3	20.9	9.0	25.2
M4.5	4.3	8.1	21.2	7.9	20.9	9.0	25.2
M4	4.3	7.2	21.2	7.2	21.2	8.3	25.2
M3.5	3.7	6.4	21.1	6.0	21.2	8.3	24.2
M3	3.2	5.7	21.1	5.6	21.0		