




## Product information BAT-ANT-N-14G-IP23

Industrial Ethernet:Industrial Wireless LAN:Accessories:Antenna:BAT-ANT-N-14G-IP23

Name	BAT-ANT-N-14G-IP23
	
	Directional antenna for 2.4 GHz with 14 dBi gain
<b>Delivery informations</b>	
<b>Product description</b>	
Description	Directional antenna for 2.4 GHz with 14 dBi gain
Type	BAT-ANT-N-14G-IP23
Order No.	943 981-005
Cable length	1 m
Cable specification	N-plug to N-plug
<b>Radio technology</b>	
Range	Please use the antenna distance calculator.
Frequency band	2400 - 2500 MHz
Polarisation	linear, vertical
Elevation, Azimuth	30°
VSWR	2
Gain	14 dBi
Antenna connector	N female
<b>Ambient conditions</b>	
Operating temperature	-40 °C to +80 °C
Storage/transport temperature	-40 °C to +80 °C
Wind load	10 N at 160 km/h
<b>Mechanical construction</b>	
Dimensions (W x H x D)	n/a
Mounting	wall, mast
Protection class	IP23
Material	plastic
Weight	0.3 kg
<b>Scope of delivery and accessories</b>	
Scope of delivery	antenna, 1m cable, pigtail, mounting material